





STANDARDAUSFÜHRUNGEN

- **TLA.Z:** Stahl, verzinkt.
- **TLA.SST:** Edelstahl nichtrostend, 1.4301.

SONDERAUSFÜHRUNGEN AUF ANFRAGE

- Spannverschlüsse in Stahl, unbeschichtet.
- Gegenhaken in verschiedenen Formen und Oberflächen.



TLA.Z

Code	Artikelnummer	b2	L	B	H	d	d1	b1	l1	l2	l3	f	f1	f2	f3	Maximale Tragfähigkeit [N]	Bruchlast [N]	⚖
420081	TLA.Z-16.4/102+R	16.4	102	23	11	3.2	2	13	16	44	30	34.5	12.5	12	5	550	1200	31
420061	TLA.Z-23/140.5+R	23	140.5	34	12.5	4.1	3	19	16	70	43	38	22.5	20	8	1500	3000	78
420051	TLA.Z-30/193.5+R	30	193.5	43	19	5.3	4	27	21.5	90	66	58.5	31.5	25.5	15	2000	4000	188

TLA.SST

Code	Artikelnummer	b2	L	B	H	d	d1	b1	l1	l2	l3	f	f1	f2	f3	Maximale Tragfähigkeit [N]	Bruchlast [N]	⚖
420082	TLA.SST-16.4/102+R	16.4	102	23	11	3.2	2	13	16	44	30	34.5	12.5	12	5	550	1200	31
420062	TLA.SST-23/140.5+R	23	140.5	34	12.5	4.1	3	19	16	70	43	38	22.5	20	8	1500	3000	78
420052	TLA.SST-30/193.5+R	30	193.5	43	19	5.3	4	27	21.5	90	66	58.5	31.5	25.5	15	2000	4000	188