RoHS

MATERIAL
Aluminium, epoxy resin coating, RAL 9005 black colour, matte finish.
AISI 304 stainless steel screws and nuts.

STANDARD EXECUTIONS
- **GN 191.1-B-B**: without sliding bushing.
- **GN 191.1-G-B**: with a polyamide based (PA) or polytetrafluoroethylene based (PTFE) technopolymer sliding bushing (d1).

FEATURES AND APPLICATIONS
GN 191.1 clamping connectors can normally be matched with the linear actuators.
By clamping the guide hole d_1 it is possible to adjust the actuator positioning and to lock the slider after having set up the final position. The clamping screws d_3 may be replaced by clamping kits GN 911 (see page 1782).





Code	Description	d1#	d1##	d2	d3	d4	k1	k2	l	m	d3 Clamping kit	⚖
GN.52206	GN 191.1-B18-B18-2-SW	18	-	18	M6	M3	25	25	61	39	GN 911-M6-22	77
GN.52216	GN 191.1-G18-B18-2-SW	-	18	18	M6	M3	25	25	61	39	GN 911-M6-22	77

Hole without sliding bushing.
Hole with sliding bushing.

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.