

VERSIONS

- Version **A**: without knurl
 - Version **B**: with knurl
- Steel
Zinc plated, blue passivated


FEATURES AND APPLICATIONS

Knobs GN 676.2 are used in applications where a push or pull movement is required. Their concave top gives a more comfortable thumb grip.
The version with knurl (type B) can be used as a knurled nut.



GN 676.2-A

GN 676.2-B



GN 676.2-A

Code	Description	d1	d2	d3	h1	h2	tmin	⚖
GN.29871	GN 676.2-21-M4-A	21	M 4	12.5	18	10.5	10	27
GN.29873	GN 676.2-21-M5-A	21	M 5	12.5	18	10.5	10	26
GN.29878	GN 676.2-25-M6-A	25	M 6	14.5	22.5	14	12	43
GN.29880	GN 676.2-25-M8-A	25	M 8	14.5	22.5	14	12	41
GN.29885	GN 676.2-31-M8-A	31	M 8	18.5	27	17	15	80
GN.29887	GN 676.2-31-M10-A	31	M 10	18.5	27	17	17	76

GN 676.2-B

Code	Description	d1	d2	d3	h1	h2	tmin	⚖
GN.29872	GN 676.2-21-M4-B	21	M 4	12.5	18	10.5	10	27
GN.29874	GN 676.2-21-M5-B	21	M 5	12.5	18	10.5	10	26
GN.29879	GN 676.2-25-M6-B	25	M 6	14.5	22.5	14	12	43
GN.29881	GN 676.2-25-M8-B	25	M 8	14.5	22.5	14	12	41
GN.29886	GN 676.2-31-M8-B	31	M 8	18.5	27	17	15	80
GN.29888	GN 676.2-31-M10-B	31	M 10	18.5	27	17	17	76