



MATERIAL

Brass.

WINDOW

Natural glass.

STANDARD EXECUTIONS

- **GN 743.7-A**: with technopolymer (Polysulfone) contrast screen.
- **GN 743.7-B**: without contrast screen.

MAXIMUM CONTINUOUS WORKING TEMPERATURE

100°C.

FEATURES AND APPLICATIONS


GN 743.7 oil level indicators can be used on pressurised oil tanks. The seal between the brass body and the glass window is guaranteed by a packing ring in NBR synthetic rubber.

The coupling of the conical threading (d2) with a right female threading (d4) will improve with the more threads that are in contact.

Generally to improve the tightness of this type of level indicators a sealing element like teflon ribbon is used.

SPECIAL EXECUTIONS ON REQUEST

Indicators with NPT conical threading.



GN 743.7-A

Code	Description	d1	d2	d3 For a	d4	a*	e	l1	l2	l3**	s	p***	Δ
GN.37481	GN 743.7-11-R3/8-A	11	R 3/8	16.7	Rp 3/8	6.4	22	13	6	10.1	19	1.34	19
GN.37483	GN 743.7-14-R1/2-A	14	R 1/2	21	Rp 1/2	8.2	27.5	17	7	13.2	24	1.81	33
GN.37485	GN 743.7-18-R3/4-A	18	R 3/4	26.4	Rp 3/4	9.5	31	18	8	14.5	27	1.81	50
GN.37487	GN 743.7-24-R1-A	24	R 1	33.2	Rp 1	10.4	40.5	21	9	16.8	35	2.30	93
GN.37489	GN 743.7-32-R1½-A	32	R 1½	42	Rp 1½	12.7	53	24	9	19.1	44.5	2.30	149

GN 743.7-B

Code	Description	d1	d2	d3 For a	d4	a*	e	l1	l2	l3**	s	p***	Δ
GN.37482	GN 743.7-11-R3/8-B	11	R 3/8	16.7	Rp 3/8	6.4	22	13	6	10.1	19	1.34	19
GN.37484	GN 743.7-14-R1/2-B	14	R 1/2	21	Rp 1/2	8.2	27.5	17	7	13.2	24	1.81	33
GN.37486	GN 743.7-18-R3/4-B	18	R 3/4	26.4	Rp 3/4	9.5	31	18	8	14.5	27	1.81	50
GN.37488	GN 743.7-24-R1-B	24	R 1	33.2	Rp 1	10.4	40.5	21	9	16.8	35	2.30	93
GN.37490	GN 743.7-32-R1½-B	32	R 1½	42	Rp 1½	12.7	53	24	9	19.1	44.5	2.30	149

* datum plane

** usable thread length

*** thread pitch