

MATERIAL

Nickel-plated steel bracket.
Screws and centering bushings MM-CC (see page -) in black-oxide steel.

FEATURES AND APPLICATIONS




The brackets are compatible with the pneumatic fastening clamps MM-BL-NK (see page -).
These brackets are used in applications where it is necessary to effectively block a metal sheet.

SPECIAL EXECUTIONS ON REQUEST

Y-shaped brackets are compatible with pneumatic fastening clamps MM-BL-NK (see page -), MM-BI-NK (see page -) or MM-BC-NK (see page -).

ACCESSORIES ON REQUEST

Clamping screws with ball terminal MM-RG (see page -).



Code	Description	b	d1	d2 H8 / h6	d3	h1	h2	l1	l3	l4	m1	m2	m5	△
MM.43020-NK	MM-FL-RG-20-NK	32	M8	7	M5	10	10	38	37	7.5	22	17	17	145
MM.43032-NK	MM-FL-RG-32-NK	42	M10	9	M6	12	12	54.5	48.5	10	30	25	23	339
MM.43040-NK	MM-FL-RG-40-NK	52	M12	11	M8	14	14	63	61	13.5	37	30	30	604
MM.43050-NK	MM-FL-RG-50-NK	62	M12	13	M10	16	16	73.5	83.5	13.5	44	47	40	850