


STANDARD EXECUTIONS

- AISI CF-8 Stainless Steel-precision casting, sandblasted matte finish:
- **MSM-TW-A-NI**: AISI 304 stainless steel clamping screw and nut, AISI 301 stainless steel spring.
 - **MSM-TW-B-NI**: adjustable handle for clamping GN 300.5, AISI CF-8 stainless steel lever, sand-blasted matte finish, AISI 303 stainless steel screw, AISI 301 stainless steel spring.


FEATURES AND APPLICATIONS

MSM-TW-NI pivoting connecting clamps allow the clamping of tubes or shafts. The special prism shape of the clamping parts facilitates adaptation to the tube or shaft diameter.
The pressure springs make the locking and unlocking operations quick and easy.



MSM-TW-A-NI

MSM-TW-B-NI



MSM-TW-A-NI

Code	Description	d1	d2	d3	d4	l1	l4	l5	m	⚖
500755	MSM-TW-28-8-A-NI	8	8	M6	28	33	14	5	13	164
500765	MSM-TW-32-10-A-NI	10	10	M8	32	45	20	5	15	242
500775	MSM-TW-36-12-A-NI	12	12	M8	36	47	21	5	17	297
500424	MSM-TW-46-14-A-NI	14	14	M8	46	57	25.5	6	20	461
500430	MSM-TW-46-15-A-NI	15	15	M10	46	57	25.5	6	21	485
500435	MSM-TW-46-16-A-NI	16	16	M10	46	57	25.5	6	22	488
500438	MSM-TW-56-18-A-NI	18	18	M10	56	63	28.5	6	24	688
500444	MSM-TW-56-20-A-NI	20	20	M10	56	65	28.5	8	28	785

MSM-TW-B-NI

Code	Description	d1	d2	d3	d4	l1	l2	l3	l4	l5	m	⚖
500756	MSM-TW-28-8-B-NI	8	8	M6	28	33	35	45	14	5	13	205
500766	MSM-TW-32-10-B-NI	10	10	M8	32	45	45	63	20	5	15	335
500776	MSM-TW-36-12-B-NI	12	12	M8	36	47	45	63	21	5	17	389
500427	MSM-TW-46-14-B-NI	14	14	M8	46	57	55	78	25.5	6	20	608
500433	MSM-TW-46-15-B-NI	15	15	M10	46	57	55	78	25.5	6	21	635
500436	MSM-TW-46-16-B-NI	16	16	M10	46	57	55	78	25.5	6	22	638
500441	MSM-TW-56-18-B-NI	18	18	M10	56	63	55	78	28.5	6	24	838
500447	MSM-TW-56-20-B-NI	20	20	M10	56	65	55	78	28.5	8	28	935