

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

MATERIAL

Phenolic based (PF) Duroplast, black colour, glossy finish.


STANDARD EXECUTION

Black-oxide steel hub.

- **VL.140**: with pre-drilled blind hole.
- **VL.140-FP**: not drilled.
- **VL.140-FP-A-M**: with threaded pass-through hole.
- **VL.140-FP-A**: with H7 reamed through hole.



ELESA Original design



VL.140

Code	Description	D	d-0.1	dH9	L	B	d1	d2	l1	l2	h	⚖
74101	VL.140/50	51	6	-	29	13	20	18	20	10	15	67
74201	VL.140/60	61	6	-	32	16	20	18	20	10	15	87
74301	VL.140/70	69	6	-	36	18	24	20	23	12	15	126
74401	VL.140/80	82	6	-	40	19	24	20	23	12	15	160
74501	VL.140/100	99	-	8	44	20	36	30	31	14	22	325
74601	VL.140/130	129	-	8	47	22	40	40	30	13	20	500

VL.140-FP

Code	Description	D	L	B	d1	d2	l	l2	⚖
74511	VL.140/100 FP-A	99	44	20	36	34	34	14	405
74611	VL.140/130 FP-A	129	47	22	40	36	34	13	560

VL.140-FP-A-M

Code	Description	D	d6H	L	B	d1	d2	d3	l	l2	a	⚖
74517	VL.140/100 FP-A-M16	99	M16	44	20	36	34	21.4	34	14	1.5	360

VL.140-FP-A

Code	Description	D	dH7	L	B	d1	d2	d3	l	l2	a	⚖
74514	VL.140/100 FP-A-16	99	16	44	20	36	34	21.4	34	14	1.5	350

Clamping elements