



ESECUZIONE STANDARD


Impugnatura I.622 in tecnopolimero, colore nero, finitura lucida, fissata al braccio in acciaio zincato, non rimovibile.

ESECUZIONI SPECIALI A RICHIESTA

Impugnatura in diversi colori RAL.



ELESA Original design



BL.668

Codice	Descrizione	A	D	L	d6g	B	b	l	△△
5011	BL.668/10x57	57	20	32	M8	25	10	9	31
5012	BL.668/10x67	67	20	32	M8	35	10	9	37
5013	BL.668/10x77	77	20	32	M8	45	10	9	43
5015	BL.668/10x107	107	20	32	M8	75	10	9	62
5016	BL.668/10x137	137	20	32	M8	105	10	11	81
5021	BL.668/12x79	79	26	42	M10	37	12	14	65
5022	BL.668/12x95	95	26	42	M10	53	12	14	79
5023	BL.668/12x142	142	26	42	M10	100	12	14	122
5024	BL.668/12x180	180	26	42	M10	138	12	14	154
5031	BL.668/14x100	100	33	55	M12	45	14	15	120
5032	BL.668/14x135	135	33	55	M12	80	14	15	156
5033	BL.668/14x175	175	33	55	M12	120	14	15	216
5041	BL.668/16x70	70	33	55	M14	15	16	15	96
5042	BL.668/16x108	108	33	55	M14	53	16	15	154
5043	BL.668/16x129	129	33	55	M14	74	16	15	186
5044	BL.668/16x155	155	33	55	M14	100	16	15	228

Impugnatura