



MATERIALE

Acciaio INOX AISI 316L, finitura mat da sabbiatura.

ESECUZIONE STANDARD

Mozzo, foro filettato passante.



INOX
STAINLESS
STEEL

Codice	Descrizione	d1	d2	d3	h	k	⚖
GN.29502	DIN 466-M3-A4	M 3	12	6	7.5	2.5	3
GN.29512	DIN 466-M4-A4	M 4	16	8	9.5	3.5	7
GN.29522	DIN 466-M5-A4	M 5	20	10	11.5	4	13
GN.29532	DIN 466-M6-A4	M 6	24	12	15	5	24
GN.29542	DIN 466-M8-A4	M 8	30	16	18	6	91
GN.29552	DIN 466-M10-A4	M 10	36	20	23	8	125