



GN 241-V

Codice	Descrizione	s Foro quadro	d2	k	l1	l2	l3	d2 Kit di serraggio	⚖
GN.56311	GN 241-V20-50-2-BL	20x20	M8	50	68	46	48	GN 911-63-M8-40 / GN 911-78-M8-40	210
GN.56331	GN 241-V25-50-2-BL	25x25	M8	50	68	46	48	GN 911-63-M8-40 / GN 911-78-M8-40	180
GN.56351	GN 241-V30-50-2-BL	30x30	M8	50	68	46	48	GN 911-63-M8-40 / GN 911-78-M8-40	160
GN.56371	GN 241-V30-60-2-BL	30x30	M8	60	79	59	58	GN 911-63-M8-40 / GN 911-78-M8-40	376
GN.56391	GN 241-V35-60-2-BL	35x35	M8	60	79	59	58	GN 911-63-M8-40 / GN 911-78-M8-40	350
GN.56411	GN 241-V40-60-2-BL	40x40	M8	60	79	59	58	GN 911-63-M8-40 / GN 911-78-M8-40	300
GN.56431	GN 241-V40-76-2-BL	40x40	M10	76	98	70	73	GN 911-78-M10-78 / GN 911-92-M10-92	450
GN.56451	GN 241-V45-76-2-BL	45x45	M10	76	98	70	73	GN 911-78-M10-78 / GN 911-92-M10-92	420
GN.56471	GN 241-V50-76-2-BL	50x50	M10	76	98	70	73	GN 911-78-M10-78 / GN 911-92-M10-92	400
GN.56481	GN 241-V60-90-2-BL	60x60	M10	90	108.5	84	83	-	482
GN.56316	GN 241-V20-50-2-SW	20x20	M8	50	68	46	48	GN 911-63-M8-40 / GN 911-78-M8-40	210
GN.56336	GN 241-V25-50-2-SW	25x25	M8	50	68	46	48	GN 911-63-M8-40 / GN 911-78-M8-40	180
GN.56356	GN 241-V30-50-2-SW	30x30	M8	50	68	46	48	GN 911-63-M8-40 / GN 911-78-M8-40	160
GN.56376	GN 241-V30-60-2-SW	30x30	M8	60	79	59	58	GN 911-63-M8-40 / GN 911-78-M8-40	376
GN.56396	GN 241-V35-60-2-SW	35x35	M8	60	79	59	58	GN 911-63-M8-40 / GN 911-78-M8-40	350
GN.56416	GN 241-V40-60-2-SW	40x40	M8	60	79	59	58	GN 911-63-M8-40 / GN 911-78-M8-40	300
GN.56436	GN 241-V40-76-2-SW	40x40	M10	76	98	70	73	GN 911-78-M10-78 / GN 911-92-M10-92	450
GN.56456	GN 241-V45-76-2-SW	45x45	M10	76	98	70	73	GN 911-78-M10-78 / GN 911-92-M10-92	420
GN.56476	GN 241-V50-76-2-SW	50x50	M10	76	98	70	73	GN 911-78-M10-78 / GN 911-92-M10-92	400
GN.56486	GN 241-V60-90-2-SW	60x60	M10	90	108.5	84	83	-	482

