

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

**MATERIALE**

Acciaio INOX AISI 304, finitura mat da sabbatura.


**ESECUZIONI STANDARD**

Mozzo saldato.

- **VCM-SST (d)**: foro cieco alesato H7.
- **VCM-SST (d1)**: foro cieco filettato.
- **VCM-SST-p**: perno filettato.



ELESA Original design



**VCM-SST (d)**



Codice	Descrizione	D	dH7	L	d3	l2	hmin.	△
169471	VCM-SST-32-6	32	6	21	12	10	12	25
169541	VCM-SST-40-8	40	8	24	14	12	15	39
169546	VCM-SST-50-10	50	10	30	18	16.5	18	70
169551	VCM-SST-60-12	60	12	37.5	20	20	22	116

**VCM-SST (d1)**



Codice	Descrizione	D	L	d1	d3	l2	hmin.	△
169472	VCM-SST-32-M5	32	21	M5	12	10	12	27
169473	VCM-SST-32-M6	32	21	M6	12	10	12	26
169540	VCM-SST-40-M6	40	24	M6	14	12	15	41
169542	VCM-SST-40-M8	40	24	M8	14	12	15	40
169545	VCM-SST-50-M8	50	30	M8	18	16.5	18	74
169547	VCM-SST-50-M10	50	30	M10	18	16.5	18	69
169550	VCM-SST-60-M10	60	37.5	M10	20	20	22	124
169552	VCM-SST-60-M12	60	37.5	M12	20	20	22	115

**VCM-SST-p**



Codice	Descrizione	D	L	d2	d3	l	l2	△
169474	VCM-SST-32-p-M6x16	32	21	M6	12	16	10	32
169475	VCM-SST-32-p-M6x20	32	21	M6	12	20	10	33
169476	VCM-SST-32-p-M6x30	32	21	M6	12	30	10	34
169561	VCM-SST-40-p-M8x20	40	24	M8	14	20	12	52
169562	VCM-SST-40-p-M8x30	40	24	M8	14	30	12	55
169563	VCM-SST-40-p-M8x40	40	24	M8	14	40	12	59
169565	VCM-SST-40-p-M8x50	40	24	M8	14	50	12	63
169571	VCM-SST-50-p-M10x20	50	30	M10	18	20	16.5	93
169572	VCM-SST-50-p-M10x30	50	30	M10	18	30	16.5	98
169573	VCM-SST-50-p-M10x40	50	30	M10	18	40	16.5	104
169574	VCM-SST-50-p-M10x50	50	30	M10	18	50	16.5	111
169575	VCM-SST-50-p-M10x60	50	30	M10	18	60	16.5	117
169580	VCM-SST-60-p-M12x20	60	37.5	M12	20	20	20	153
169581	VCM-SST-60-p-M12x30	60	37.5	M12	20	30	20	158
169582	VCM-SST-60-p-M12x40	60	37.5	M12	20	40	20	165
169583	VCM-SST-60-p-M12x50	60	37.5	M12	20	50	20	174
169585	VCM-SST-60-p-M12x60	60	37.5	M12	20	60	20	187