

Indexing and positioning elements

CHAIN

Ball cable and coupling heads in acetal resin based (POM) technopolymer, black colour.

STANDARD EXECUTIONS

NERINOX treated stainless steel ring with two coils.

- **CT-S-2A**: cable with two clamping rings.
- **CT-S-A**: cable with one ring.
- **CT-S**: cable without rings.

FEATURES AND APPLICATIONS




CT-S chains are characterised by great flexibility with regard to the various types of cables in both metal and polyethylene.

They are mainly used in combination with the different types of self-flocking pins or in cases where you want to make small components or tools unmissable so that they are always available and at hand.

The CV-T product is recommended for chains with a higher applicable static load.



Conversion Table 1 mm = 0.039 inch			
d1		l	
mm	inch	mm	inch
16	0.62	150	5.85
18	0.70	200	7.80
24	0.94	320	12.48
30	1.17	500	19.50




CT-S-2A

Code	Description	d1	d2	l	Max. static load [N]	⚖
76301	CT-S-2A-18-150	18	1.3	150	100	8
76302	CT-S-2A-24-150	24	1.5	150	100	10
76303	CT-S-2A-30-150	30	1.8	150	100	13
76306	CT-S-2A-18-200	18	1.3	200	100	9
76307	CT-S-2A-24-200	24	1.5	200	100	11
76308	CT-S-2A-30-200	30	1.8	200	100	13
76311	CT-S-2A-18-320	18	1.3	320	100	10
76312	CT-S-2A-24-320	24	1.5	320	100	12
76313	CT-S-2A-30-320	30	1.8	320	100	15
76316	CT-S-2A-18-500	18	1.3	500	100	12
76317	CT-S-2A-24-500	24	1.5	500	100	14
76318	CT-S-2A-30-500	30	1.8	500	100	17

CT-S-A

Code	Description	d1	d2	l	Max. static load [N]	⚖
77015	CT-S-A-16-150	16	1.3	150	100	6
76321	CT-S-A-18-150	18	1.3	150	100	7
76322	CT-S-A-24-150	24	1.5	150	100	8
76323	CT-S-A-30-150	30	1.8	150	100	10
77020	CT-S-A-16-200	16	1.3	200	100	7
76326	CT-S-A-18-200	18	1.3	200	100	8
76327	CT-S-A-24-200	24	1.5	200	100	9
76328	CT-S-A-30-200	30	1.8	200	100	10
77032	CT-S-A-16-320	16	1.3	320	100	8
76331	CT-S-A-18-320	18	1.3	320	100	9
76332	CT-S-A-24-320	24	1.5	320	100	10
76333	CT-S-A-30-320	30	1.8	320	100	12
77050	CT-S-A-16-500	16	1.3	500	100	10
76336	CT-S-A-18-500	18	1.3	500	100	11
76337	CT-S-A-24-500	24	1.5	500	100	12
76338	CT-S-A-30-500	30	1.8	500	100	14



CT-S

Code	Description	l	Max. static load [N]	⚖
77016	CT-S-150	150	100	6
77021	CT-S-200	200	100	7
77033	CT-S-320	320	100	8
77051	CT-S-500	500	100	10