


- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

STANDARD EXECUTIONS

AISI 303 stainless steel, sandblasted matte finish:

- DIN 6303-A-NI: threaded pass-through hole, without transversal hole.
- DIN 6303-B-NI: threaded pass-through hole, with transversal hole.



**Conversion Table**  
1 mm = 0.039 inch

d4	
mm	inch
20	0.79
24	0.94
30	1.18
36	1.40
40	1.56

INOX STAINLESS STEEL METRIC

INOX STAINLESS STEEL METRIC

DIN 6303-A-NI

Code	Description	d1	d3	d4	h	k	l	⚖
GN.30171	DIN 6303-M5-A-NI	M5	14	20	12	8	7	17
GN.30172	DIN 6303-M6-A-NI	M6	16	24	14	10	8	30
GN.30173	DIN 6303-M8-A-NI	M8	20	30	17	12	10	50
GN.30174	DIN 6303-M10-A-NI	M10	28	36	20	14	12	90
GN.30175	DIN 6303-M12-A-NI	M12	32	40	24	16	16	133

DIN 6303-B-NI

Code	Description	d1	d3	d4	d5 H11	h	e	k	l	⚖
GN.30181	DIN 6303-M5-B-NI	M5	14	20	1.5	12	2.5	8	7	18
GN.30182	DIN 6303-M6-B-NI	M6	16	24	1.5	14	2.5	10	8	29
GN.30183	DIN 6303-M8-B-NI	M8	20	30	2	17	3	12	10	45
GN.30184	DIN 6303-M10-B-NI	M10	28	36	3	20	4	14	12	45
GN.30185	DIN 6303-M12-B-NI	M12	32	40	4	24	4	16	16	89

Clamping elements