

MATERIAL

Aluminium, matte finish.
AISI 304 stainless steel screws and nuts.

STANDARD EXECUTIONS


Surface finish index:
- **BL**: natural colour.
- **SW**: epoxy resin coating resistant to UV rays, RAL 9005 black colour.

FEATURES AND APPLICATIONS


The assembly holes of GN 131 connecting clamps allow an excellent match with tubes GN 990 (see page 1368).
The clamping screw d3 may be replaced by clamping kit GN 911 (see page 1372).

SPECIAL EXECUTIONS ON REQUEST

Different combinations of holes d1/d2.



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
10	0.39
12	0.47
14	0.55
15	0.59
16	0.63
18	0.71



Code BL	Code SW	Description	d1	d2	d3	k	l	m	d3 Clamping kit	⚖
GN.42011	GN.42016	GN 131-B10-B10-2-*	10	10	M6	25	64	20	GN 911-M6-22	86
GN.42031	GN.42036	GN 131-B12-B12-2-*	12	12	M6	25	64	20	GN 911-M6-22	80
GN.42051	GN.42056	GN 131-B14-B14-2-*	14	14	M6	25	64	20	GN 911-M6-22	68
GN.42071	GN.42076	GN 131-B15-B15-2-*	15	15	M6	25	64	20	GN 911-M6-22	65
GN.42091	GN.42096	GN 131-B16-B16-2-*	16	16	M6	25	64	20	GN 911-M6-22	73
GN.42111	GN.42116	GN 131-B18-B18-2-*	18	18	M6	25	64	20	GN 911-M6-22	68

* Complete the description of the standard item needed by adding the finish of the connector clamps: BL (blank) or SW (black).