

MATERIAL

AISI 303 stainless steel.


STANDARD EXECUTIONS

- **GN 5335-A:** sandblasted matte finish, without hole.
- **GN 5335-C:** sandblasted matte finish, H7 reamed blind hole.
- **GN 5335-E:** sandblasted matte finish, threaded blind hole.
- **GN 5335-E-PL:** polished, threaded blind hole.
- **GN 5335-D:** sandblasted matte finish, threaded pass-through hole.
- **GN 5335-D-PL:** polished, threaded pass-through hole.
- **GN 5335:** sandblasted matte finish, threaded pin.

FEATURES AND APPLICATIONS

The finish quality, angular seal and absence of recesses, prevents dirt adherence and facilitates cleaning. Particularly suitable for applications on machines and equipment whose parts must be frequently cleaned by using water jets or steam.

Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
40	1.57
50	1.97
60	2.34



GN 5335-A

Code	Description	d1	d4	h1	h2	Δ
GN.28548	GN 5335-40-A	40	18	30.5	15	130
GN.28558	GN 5335-50-A	50	21	34	17	220
GN.28566	GN 5335-60-A	60	25	39	18	388

GN 5335-C

Code	Description	d1	d3 H7	d4	h1	h2	t1 min	Δ
GN.28601	GN 5335-40-B8-C	40	B 8	18	30.5	15	15	125
GN.28611	GN 5335-50-B10-C	50	B 10	21	34	17	18	205
GN.28567	GN 5335-60-B10-C	60	B 10	25	39	18	18	370
GN.28621	GN 5335-60-B12-C	60	B 12	25	39	18	22	366


GN 5335-E

Code	Description	d1	d2	d4	h1	h2	t1 min	Δ
GN.28605	GN 5335-40-M6-E	40	M 6	18	30.5	15	12	140
GN.28606	GN 5335-40-M8-E	40	M 8	18	30.5	15	15	135
GN.28615	GN 5335-50-M8-E	50	M 8	21	34	17	15	240
GN.28616	GN 5335-50-M10-E	50	M 10	21	34	17	18	235
GN.28625	GN 5335-60-M10-E	60	M 10	25	39	18	18	391
GN.28626	GN 5335-60-M12-E	60	M 12	25	39	18	22	389


GN 5335-E-PL

Code	Description	d1	d2	d4	h1	h2	t1 min	Δ
GN.28552	GN 5335-40-M6-E-PL	40	M 6	18	30.5	15	12	140
GN.28557	GN 5335-40-M8-E-PL	40	M 8	18	30.5	15	15	140
GN.28565	GN 5335-50-M8-E-PL	50	M 8	21	34	17	15	240
GN.28562	GN 5335-50-M10-E-PL	50	M 10	21	34	17	18	240
GN.28570	GN 5335-60-M10-E-PL	60	M 10	25	39	18	18	391
GN.28573	GN 5335-60-M12-E-PL	60	M 12	25	39	18	22	400


**GN 5335-E
GN 5335-E-PL**



**GN 5335-D
GN 5335-D-PL**



GN 5335



GN 5335-D

Code	Description	d1	d2	d4	h1	h2	t2	Δ
GN.28549	GN 5335-40-M6-D	40	M 6	18	30.5	15	13	132
GN.28554	GN 5335-40-M8-D	40	M 8	18	30.5	15	13	130
GN.28563	GN 5335-50-M8-D	50	M 8	21	34	17	16	225
GN.28560	GN 5335-50-M10-D	50	M 10	21	34	17	16	205
GN.28568	GN 5335-60-M10-D	60	M 10	25	39	18	20	370
GN.28571	GN 5335-60-M12-D	60	M 12	25	39	18	20	366

GN 5335-D-PL

Code	Description	d1	d2	d4	h1	h2	t2	Δ
GN.28550	GN 5335-40-M6-D-PL	40	M 6	18	30.5	15	13	132
GN.28556	GN 5335-40-M8-D-PL	40	M 8	18	30.5	15	13	130
GN.28564	GN 5335-50-M8-D-PL	50	M 8	21	34	17	16	225
GN.28561	GN 5335-50-M10-D-PL	50	M 10	21	34	17	16	205
GN.28569	GN 5335-60-M10-D-PL	60	M 10	25	39	18	20	370
GN.28572	GN 5335-60-M12-D-PL	60	M 12	25	39	18	20	366

GN 5335

Code	Description	d1	d2	d4	l	h1	h2	Δ
GN.28607	GN 5335-40-M8-16	40	M 8	18	16	30.5	15	140
GN.28608	GN 5335-40-M8-20	40	M 8	18	20	30.5	15	151
GN.28609	GN 5335-40-M8-25	40	M 8	18	25	30.5	15	180
GN.28617	GN 5335-50-M10-20	50	M 10	21	20	34	17	245
GN.28618	GN 5335-50-M10-25	50	M 10	21	25	34	17	247
GN.28619	GN 5335-50-M10-30	50	M 10	21	30	34	17	270
GN.28627	GN 5335-60-M12-25	60	M 12	25	25	39	18	420
GN.28628	GN 5335-60-M12-30	60	M 12	25	30	39	18	426
GN.28629	GN 5335-60-M12-40	60	M 12	25	40	39	18	441