METRIC


INOX STAINLESS STEEL

RoHS


MATERIAL
AISI 304 pressed stainless steel, sandblasted matte finish.

STANDARD EXECUTIONS
- **GN 227.2-A**: without handle.
- **GN 227.2-D**: with revolving handle in phenolic based (PF) Duroplast, black colour, glossy finish.


Hole index:
- **B**: welded hub H9 reamed hole.
- **V**: welded hub H11 square hole.




GN 227.2-A-B




GN 227.2-A-V



GN 227.2-D-B



GN 227.2-D-V



Conversion Table
1 mm = 0.039 inch

d1	
mm	**inch**
160	**6.30**
200	**7.87**
250	**9.84**
315	**12.40**
400	**15.75**

GN 227.2-A

INOX STAINLESS STEEL METRIC

Code	Description	d1	d2 H9	sH11	d3	b	l1	l2	Spokes no.	Thickness stainless steel	⚖
GN.25281	GN 227.2-160-B12-A	160	12	-	30	22	20	39	4	2	430
GN.25291	GN 227.2-200-B14-A	200	14	-	40	22	24	44	4	2.5	824
GN.25301	GN 227.2-250-B17-A	250	17	-	45	30	28	52	5	3	1477
GN.25307	GN 227.2-315-B19-A	315	19	-	55	36	33	64	5	3	2330
GN.25315	GN 227.2-400-B24-A	400	24	-	65	43	38	81	5	3	4210
GN.25285	GN 227.2-160-V12-A	160	-	12	30	22	20	39	4	2	428
GN.25295	GN 227.2-200-V14-A	200	-	14	40	22	24	44	4	2.5	824
GN.25305	GN 227.2-250-V17-A	250	-	17	45	30	28	52	5	3	1465
GN.25308	GN 227.2-315-V19-A	315	-	19	55	36	33	64	5	3	2100
GN.25316	GN 227.2-400-V24-A	400	-	24	65	43	38	81	5	3	4180

GN 227.2-D

INOX STAINLESS STEEL METRIC

Code	Description	d1	d2 H9	sH11	d3	b	l1	l2	l3	r	d7	Spokes no.	Thickness stainless steel	⚖
GN.25321	GN 227.2-160-B12-D	160	12	-	30	22	20	39	83	68	26	4	2	530
GN.25331	GN 227.2-200-B14-D	200	14	-	40	22	24	44	83	88	26	4	2.5	924
GN.25341	GN 227.2-250-B17-D	250	17	-	45	30	28	52	93	108	28	5	3	1565
GN.25351	GN 227.2-315-B19-D	315	19	-	55	36	33	64	93	138	28	5	3	2400
GN.25357	GN 227.2-400-B24-D	400	24	-	65	43	38	81	93	178	28	5	3	4300
GN.25325	GN 227.2-160-V12-D	160	-	12	30	22	20	39	83	68	26	4	2	528
GN.25335	GN 227.2-200-V14-D	200	-	14	40	22	24	44	83	88	26	4	2.5	924
GN.25345	GN 227.2-250-V17-D	250	-	17	45	30	28	52	93	108	28	5	3	1565
GN.25352	GN 227.2-315-V19-D	315	-	19	55	36	33	64	93	138	28	5	3	2700
GN.25359	GN 227.2-400-V24-D	400	-	24	65	43	38	81	93	178	28	5	3	4300

elesa
All rights reserved in accordance with the law. Always mention the source when reproducing our drawings.