

MATERIAL

Nickel-plated steel bracket.
Screws and centering bushings MM-CC (see page -) in black-oxide steel.

FEATURES



The brackets are compatible with the pneumatic fastening clamps MM-BL-NK (see page -).

SPECIAL EXECUTIONS ON REQUEST

Y-shaped brackets are compatible with pneumatic fastening clamps MM-BL-NK (see page -), MM-BI-NK (see page -) or MM-BC-NK (see page -).

ACCESSORIES ON REQUEST

Clamping screws with ball terminal MM-RG (see page -).



Conversion Table	
1 mm = 0.039 inch	
b	
mm	inch
32	1.25
42	1.64
52	2.03
62	2.42

Code	Description	b	d1	d2 H8 / h6	d3	h1	h2	l1	l2	l3	l4	m1	m2	△
MM.44020-NK	MM-FL-RG1-20-NK	32	M8	7	M5	10	10	38	13	37	7.5	22	17	121
MM.44032-NK	MM-FL-RG1-32-NK	42	M10	9	M6	12	12	54.5	17	48.5	10	30	25	261
MM.44044-NK	MM-FL-RG1-40-NK	52	M12	11	M8	14	14	63	20	61	13.5	37	30	471
MM.44050-NK	MM-FL-RG1-50-NK	62	M12	13	M10	16	16	73.5	20	83.5	13.5	44	47	779