Mounting guides

For RCG roller chain guides, steel or stainless steel

INOX STAINLESS STEEL RoHS

STANDARD EXECUTIONS

- **RCG-GU-ZN:** zinc-plated steel.
- **RCG-GU-SST:** AISI 304 stainless steel.

FEATURES AND APPLICATIONS

C-shaped structural supports for positioning and securing the various RCG guides.
Available in various sizes to suit different guides: the RCG-GU-3 features a reduced cross-section for small chains or tight spaces, while the RCG-GU-5 and RCG-GU-9 feature medium cross-sections and are typically used in light industrial automation.
They are supplied in 2000 mm long bars.


ACCESSORIES


RCG-CE: Roller chain guide type CE.
RCG-CT: Roller chain guide type CT.
RCG-CP: Roller chain guide type CP.



Application example

RCG-CE RCG-CT RCG-CP





RCG-GU-ZN

Code	Description	h	b	b_1	s	⚖
506306	RCG-GU-3-20-10-2000-ZN	10	20	10	1.5	980
506316	RCG-GU-5-28-12-2000-ZN	12	28	14	2	1700
506326	RCG-GU-9-38-18-2000-ZN	18	38	22	2.5	3000

RCG-GU-SST

INOX STAINLESS STEEL

Code	Description	h	b	b_1	s	⚖
506301	RCG-GU-3-20-10-2000-SST	10	20	10	1.5	980
506311	RCG-GU-5-28-12-2000-SST	12	28	14	2	1700
506321	RCG-GU-9-38-18-2000-SST	18	38	22	2.5	3000

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.