

STANDARD EXECUTIONS


- **TLAS.Z:** lever body and bracket in zinc-plated steel with spring.
- **TLAS.NH:** lever body and bracket in nickel-plated steel, RAL 3000 red technopolymer push button.
- **TLAS.SST-16.4:** lever body and bracket in AISI 304 stainless steel with spring.
- **TLAS.SST-30:** lever body and bracket in AISI 304 stainless steel, RAL 3000 red technopolymer push button.

SPECIAL EXECUTIONS ON REQUEST


- Hook clamps in unplated steel.
- Catch brackets in different shapes and finishes.



TLAS.NH-30/193.5+R
TLAS.SST-30/193.5+R



TLAS.Z-16.4/102+R
TLAS.SST-16.4/102+R



Conversion Table 1 mm = 0.039 inch			
b2		L	
mm	inch	mm	inch
16.4	0.64	102	4.02
30	1.18	193.5	7.62

