Breather caps

with splash guard, technopolymer

RoHS PA +100° -30°

COVER
Polyamide based (PA) technopolymer, semi-matte finish.
- SFP.....: RAL 2004 orange, marked “OIL”.
- SFP.....-C9: RAL 9005 black colour, marked “OIL”.
- SFP.....-C2-N: RAL 2004 orange, without “OIL” mark.
- SFP.....-C9-N: RAL 9005 black colour, without “OIL” mark.

THREADED FITTING
Polyamide based (PA) technopolymer, black colour, semi-matte finish.

PACKING RING
NBR synthetic rubber.

SPLASH GUARD
Technopolymer.

STANDARD EXECUTIONS
- **SFP.**: without air filter (black splash guard).
- **SFP+F-FIL**: with “tech-fil” air filter in zinc-plated steel wire (orange splash guard).
- **SFP+F-FOAM**: with “tech-foam” air filter in polyurethane foam mesh (polyester base), air filtration 40 µ (grey splash guard).
- **SFP-BA+F**: with “tech-foam” air filter in polyurethane foam mesh (polyester base), air filtration 40 µ (grey splash guard).

Zinc-plated steel sheet bayonet.
Chrome-plated steel safety chain.

MAXIMUM CONTINUOUS WORKING TEMPERATURE
100°C.


FEATURES AND APPLICATIONS
SFP. breather caps come complete with splash guard device (ELESA original design) that prevents oil loss and are particularly suitable for use where oil is violently agitated and could be splashed against breather cap.


TECHNICAL DATA
Air flow rate for each model can be determined from the graph calculating the difference between the pressure inside and outside the reservoir.




ELESA Original design

Operating layout








elesa 10/2026


Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.



SFP.

Code	Description	D	L	d	d_2	h	⚖
54141	SFP.30-12x1.5	31	29.5	M12x1.5	6	9.5	12
54141-C9	SFP.30-12x1.5-C9	31	29.5	M12x1.5	6	9.5	12
54161	SFP.30-14x1.5	31	29.5	M14x1.5	8	9.5	12
54161-C9	SFP.30-14x1.5-C9	31	29.5	M14x1.5	8	9.5	12
53941	SFP.30-16x1.5	31	29.5	M16x1.5	10	9.5	12
53941-C9	SFP.30-16x1.5-C9	31	29.5	M16x1.5	10	9.5	12
53961	SFP.30-18x1.5	31	29.5	M18x1.5	10	9.5	12
53961-C9	SFP.30-18x1.5-C9	31	29.5	M18x1.5	10	9.5	12
53981	SFP.30-20x1.5	31	29.5	M20x1.5	12	9.5	12
53981-C9	SFP.30-20x1.5-C9	31	29.5	M20x1.5	12	9.5	12
53991	SFP.30-22x1.5	31	29.5	M22x1.5	12	9.5	13
53991-C9	SFP.30-22x1.5-C9	31	29.5	M22x1.5	12	9.5	13
54341	SFP.40-24x1.5	42	36.5	M24x1.5	18	11.5	25
54341-C9	SFP.40-24x1.5-C9	42	36.5	M24x1.5	18	11.5	25
54361	SFP.40-26x1.5	42	36.5	M26x1.5	18	11.5	16
54361-C9	SFP.40-26x1.5-C9	42	36.5	M26x1.5	18	11.5	16
53935	SFP.30-1/4	31	29.5	G 1/4	8	9.5	12
53935-C9	SFP.30-1/4-C9	31	29.5	G 1/4	8	9.5	12
54001	SFP.30-3/8	31	29.5	G 3/8	10	9.5	12
54001-C9	SFP.30-3/8-C9	31	29.5	G 3/8	10	9.5	12
54101	SFP.30-1/2	31	29.5	G 1/2	12	9.5	12
54101-C9	SFP.30-1/2-C9	31	29.5	G 1/2	12	9.5	12
56651	SFP.40-3/8	42	36.5	G 3/8	10	11.5	22
56651-C9	SFP.40-3/8-C9	42	36.5	G 3/8	10	11.5	22
56671	SFP.40-1/2	42	36.5	G 1/2	12	11.5	24
56671-C9	SFP.40-1/2-C9	42	36.5	G 1/2	12	11.5	24
54201	SFP.40-3/4	42	36.5	G 3/4	18	11.5	26
54201-C9	SFP.40-3/4-C9	42	36.5	G 3/4	18	11.5	25
54301	SFP.40-1	42	36.5	G 1	18	11.5	26
54301-C9	SFP.40-1-C9	42	36.5	G 1	18	11.5	26
56701	SFP.57-3/4	57	42	G 3/4	18	14	43
56701-C9	SFP.57-3/4-C9	57	42	G 3/4	18	14	43
56731	SFP.57-1	57	42	G 1	23	14	43
56731-C9	SFP.57-1-C9	57	42	G 1	23	14	43
54401	SFP.57-1¼	57	44	G 1 1/4	28	16	46
54401-C9	SFP.57-1¼-C9	57	44	G 1 1/4	28	16	46
54501	SFP.57-1½	57	44	G 1 1/2	28	16	47
54501-C9	SFP.57-1½-C9	57	44	G 1 1/2	28	16	46
54876	SFP.70-2	70	59	G 2	23	17	91
54876-C9	SFP.70-2-C9	70	59	G 2	23	17	91


Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.



SFP-N

Code	Description	D	L	d	d_2	h	⚖
54141-C2-N	SFP.30-12x1.5-C2-N	31	29.5	M12x1.5	6	9.5	12
54141-C9-N	SFP.30-12x1.5-C9-N	31	29.5	M12x1.5	6	9.5	12
54161-C2-N	SFP.30-14x1.5-C2-N	31	29.5	M14x1.5	8	9.5	12
54161-C9-N	SFP.30-14x1.5-C9-N	31	29.5	M14x1.5	8	9.5	12
53941-C2-N	SFP.30-16x1.5-C2-N	31	29.5	M16x1.5	10	9.5	12
53941-C9-N	SFP.30-16x1.5-C9-N	31	29.5	M16x1.5	10	9.5	12
53961-C2-N	SFP.30-18x1.5-C2-N	31	29.5	M18x1.5	10	9.5	12
53961-C9-N	SFP.30-18x1.5-C9-N	31	29.5	M18x1.5	10	9.5	12
53981-C2-N	SFP.30-20x1.5-C2-N	31	29.5	M20x1.5	12	9.5	12
53981-C9-N	SFP.30-20x1.5-C9-N	31	29.5	M20x1.5	12	9.5	12
53991-C2-N	SFP.30-22x1.5-C2-N	31	29.5	M22x1.5	12	9.5	13
53991-C9-N	SFP.30-22x1.5-C9-N	31	29.5	M22x1.5	12	9.5	13
54341-C2-N	SFP.40-24x1.5-C2-N	42	36.5	M24x1.5	18	11.5	25
54341-C9-N	SFP.40-24x1.5-C9-N	42	36.5	M24x1.5	18	11.5	25
54361-C2-N	SFP.40-26x1.5-C2-N	42	36.5	M26x1.5	18	11.5	16
54361-C9-N	SFP.40-26x1.5-C9-N	42	36.5	M26x1.5	18	11.5	16
53935-C2-N	SFP.30-1/4-C2-N	31	29.5	G 1/4	8	9.5	12
53935-C9-N	SFP.30-1/4-C9-N	31	29.5	G 1/4	8	9.5	12
54001-C2-N	SFP.30-3/8-C2-N	31	29.5	G 3/8	10	9.5	12
54001-C9-N	SFP.30-3/8-C9-N	31	29.5	G 3/8	10	9.5	12
54101-C2-N	SFP.30-1/2-C2-N	31	29.5	G 1/2	12	9.5	12
54101-C9-N	SFP.30-1/2-C9-N	31	29.5	G 1/2	12	9.5	12
56651-C2-N	SFP.40-3/8-C2-N	42	36.5	G 3/8	10	11.5	23
56651-C9-N	SFP.40-3/8-C9-N	42	36.5	G 3/8	10	11.5	22
56671-C2-N	SFP.40-1/2-C2-N	42	36.5	G 1/2	12	11.5	24
56671-C9-N	SFP.40-1/2-C9-N	42	36.5	G 1/2	12	11.5	24
54201-C2-N	SFP.40-3/4-C2-N	42	36.5	G 3/4	18	11.5	25
54201-C9-N	SFP.40-3/4-C9-N	42	36.5	G 3/4	18	11.5	25
54301-C2-N	SFP.40-1-C2-N	42	36.5	G 1	18	11.5	26
54301-C9-N	SFP.40-1-C9-N	42	36.5	G 1	18	11.5	26
56701-C2-N	SFP.57-3/4-C2-N	57	42	G 3/4	18	14	43
56701-C9-N	SFP.57-3/4-C9-N	57	42	G 3/4	18	14	43
56731-C2-N	SFP.57-1-C2-N	57	42	G 1	23	14	43
56731-C9-N	SFP.57-1-C9-N	57	42	G 1	23	14	43
54401-C2-N	SFP.57-1¼-C2-N	57	44	G 1 1/4	28	16	46
54401-C9-N	SFP.57-1¼-C9-N	57	44	G 1 1/4	28	16	46
54501-C2-N	SFP.57-1½-C2-N	57	44	G 1 1/2	28	16	46
54501-C9-N	SFP.57-1½-C9-N	57	44	G 1 1/2	28	16	46
54876-C2-N	SFP.70-2-C2-N	70	59	G 2	23	17	91
54876-C9-N	SFP.70-2-C9-N	70	59	G 2	23	17	91


Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.



SFP+F-FIL

Code	Description	D	L	d	d_2	h	⚖
54151	SFP.30-12x1.5+F FIL	31	29.5	M12x1.5	6	9.5	13
54151-C9	SFP.30-12x1.5+F FIL-C9	31	29.5	M12x1.5	6	9.5	13
54171	SFP.30-14x1.5+F FIL	31	29.5	M14x1.5	8	9.5	13
54171-C9	SFP.30-14x1.5+F FIL-C9	31	29.5	M14x1.5	8	9.5	13
53951	SFP.30-16x1.5+F FIL	31	29.5	M16x1.5	10	9.5	13
53951-C9	SFP.30-16x1.5+F FIL-C9	31	29.5	M16x1.5	10	9.5	13
53971	SFP.30-18x1.5+F FIL	31	29.5	M18x1.5	10	9.5	14
53971-C9	SFP.30-18x1.5+F FIL-C9	31	29.5	M18x1.5	10	9.5	14
53986	SFP.30-20x1.5+F FIL	31	29.5	M20x1.5	12	9.5	14
53986-C9	SFP.30-20x1.5+F FIL-C9	31	29.5	M20x1.5	12	9.5	14
53996	SFP.30-22x1.5+F FIL	31	29.5	M22x1.5	12	9.5	16
53996-C9	SFP.30-22x1.5+F FIL-C9	31	29.5	M22x1.5	12	9.5	16
54351	SFP.40-24x1.5+F FIL	42	36.5	M24x1.5	18	11.5	30
54351-C9	SFP.40-24x1.5+F FIL-C9	42	36.5	M24x1.5	18	11.5	30
54371	SFP.40-26x1.5+F FIL	42	36.5	M26x1.5	18	11.5	20
54371-C9	SFP.40-26x1.5+F FIL-C9	42	36.5	M26x1.5	18	11.5	20
53937	SFP.30-1/4+F FIL	31	29.5	G 1/4	8	9.5	13
53937-C9	SFP.30-1/4+F FIL-C9	31	29.5	G 1/4	8	9.5	13
54021	SFP.30-3/8+F FIL	31	29.5	G 3/8	10	9.5	13
54021-C9	SFP.30-3/8+F FIL-C9	31	29.5	G 3/8	10	9.5	13
54121	SFP.30-1/2+F FIL	31	29.5	G 1/2	12	9.5	14
54121-C9	SFP.30-1/2+F FIL-C9	31	29.5	G 1/2	12	9.5	14
56661	SFP.40-3/8+F FIL	42	36.5	G 3/8	10	11.5	28
56661-C9	SFP.40-3/8+F FIL-C9	42	36.5	G 3/8	10	11.5	28
56681	SFP.40-1/2+F FIL	42	36.5	G 1/2	12	11.5	29
56681-C9	SFP.40-1/2+F FIL-C9	42	36.5	G 1/2	12	11.5	29
54221	SFP.40-3/4+F FIL	42	36.5	G 3/4	18	11.5	30
54221-C9	SFP.40-3/4+F FIL-C9	42	36.5	G 3/4	18	11.5	30
54321	SFP.40-1+F FIL	42	36.5	G 1	18	11.5	32
54321-C9	SFP.40-1+F FILC9	42	36.5	G 1	18	11.5	32
56711	SFP.57-3/4+F FIL	57	42	G 3/4	18	14	51
56711-C9	SFP.57-3/4+F FIL-C9	57	42	G 3/4	18	14	51
56741	SFP.57-1+F FIL	57	42	G 1	23	14	52
56741-C9	SFP.57-1+F FIL-C9	57	42	G 1	23	14	52
54421	SFP.57-1¼+F FIL	57	44	G 1 1/4	28	16	55
54421-C9	SFP.57-1¼+F FIL-C9	57	44	G 1 1/4	28	16	55
54521	SFP.57-1½+F FIL	57	44	G 1 1/2	28	16	56
54521-C9	SFP.57-1½+F FIL-C9	57	44	G 1 1/2	28	16	56

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.





SFP+F-FIL-N

Code	Description	D	L	d	d_2	h	⚖
54151-C2-N	SFP.30-12x1.5+F FIL-C2-N	31	29.5	M12x1.5	6	9.5	13
54151-C9-N	SFP.30-12x1.5+F FIL-C9-N	31	29.5	M12x1.5	6	9.5	13
54171-C2-N	SFP.30-14x1.5+F FIL-C2-N	31	29.5	M14x1.5	8	9.5	13
54171-C9-N	SFP.30-14x1.5+F FIL-C9-N	31	29.5	M14x1.5	8	9.5	13
53951-C2-N	SFP.30-16x1.5+F FIL-C2-N	31	29.5	M16x1.5	10	9.5	13
53951-C9-N	SFP.30-16x1.5+F FIL-C9-N	31	29.5	M16x1.5	10	9.5	13
53971-C2-N	SFP.30-18x1.5+F FIL-C2-N	31	29.5	M18x1.5	10	9.5	14
53971-C9-N	SFP.30-18x1.5+F FIL-C9-N	31	29.5	M18x1.5	10	9.5	14
53986-C2-N	SFP.30-20x1.5+F FIL-C2-N	31	29.5	M20x1.5	12	9.5	14
53986-C9-N	SFP.30-20x1.5+F FIL-C9-N	31	29.5	M20x1.5	12	9.5	14
53996-C2-N	SFP.30-22x1.5+F FIL-C2-N	31	29.5	M22x1.5	12	9.5	16
53996-C9-N	SFP.30-22x1.5+F FIL-C9-N	31	29.5	M22x1.5	12	9.5	16
54351-C2-N	SFP.40-24x1.5+F FIL-C2-N	42	36.5	M24x1.5	18	11.5	30
54351-C9-N	SFP.40-24x1.5+F FIL-C9-N	42	36.5	M24x1.5	18	11.5	30
54371-C2-N	SFP.40-26x1.5+F FIL-C2-N	42	36.5	M26x1.5	18	11.5	20
54371-C9-N	SFP.40-26x1.5+F FIL-C9-N	42	36.5	M26x1.5	18	11.5	20
53937-C2-N	SFP.30-1/4+F FIL-C2-N	31	29.5	G 1/4	8	9.5	13
53937-C9-N	SFP.30-1/4+F FIL-C9-N	31	29.5	G 1/4	8	9.5	13
54021-C2-N	SFP.30-3/8+F FIL-C2-N	31	29.5	G 3/8	10	9.5	13
54021-C9-N	SFP.30-3/8+F FIL-C9-N	31	29.5	G 3/8	10	9.5	13
54121-C2-N	SFP.30-1/2+F FIL-C2-N	31	29.5	G 1/2	12	9.5	14
54121-C9-N	SFP.30-1/2+F FIL-C9-N	31	29.5	G 1/2	12	9.5	14
56661-C2-N	SFP.40-3/8+F FIL-C2-N	42	36.5	G 3/8	10	11.5	28
56661-C9-N	SFP.40-3/8+F FIL-C9-N	42	36.5	G 3/8	10	11.5	28
56681-C2-N	SFP.40-1/2+F FIL-C2-N	42	36.5	G 1/2	12	11.5	29
56681-C9-N	SFP.40-1/2+F FIL-C9-N	42	36.5	G 1/2	12	11.5	29
54221-C2-N	SFP.40-3/4+F FIL-C2-N	42	36.5	G 3/4	18	11.5	30
54221-C9-N	SFP.40-3/4+F FIL-C9-N	42	36.5	G 3/4	18	11.5	30
54321-C2-N	SFP.40-1+F FIL-C2-N	42	36.5	G 1	18	11.5	32
54321-C9-N	SFP.40-1+F FIL-C9-N	42	36.5	G 1	18	11.5	32
56711-C2-N	SFP.57-3/4+F FIL-C2-N	57	42	G 3/4	18	14	51
56711-C9-N	SFP.57-3/4+F FIL-C9-N	57	42	G 3/4	18	14	51
56741-C2-N	SFP.57-1+F FIL-C2-N	57	42	G 1	23	14	52
56741-C9-N	SFP.57-1+F FIL-C9-N	57	42	G 1	23	14	52
54421-C2-N	SFP.57-1¼+F FIL-C2-N	57	44	G 1 1/4	28	16	55
54421-C9-N	SFP.57-1¼+F FIL-C9-N	57	44	G 1 1/4	28	16	55
54521-C2-N	SFP.57-1½+F FIL-C2-N	57	44	G 1 1/2	28	16	56
54521-C9-N	SFP.57-1½+F FIL-C9-N	57	44	G 1 1/2	28	16	56

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.








SFP+F-FOAM

Code	Description	D	L	d	d_2	d_3	h	h_1	⚖
54152	SFP.30-12x1.5+F FOAM	31	29.5	M12x1.5	6	-	9.5	-	11
54152-C9	SFP.30-12x1.5+F FOAM-C9	31	29.5	M12x1.5	6	-	9.5	-	11
54172	SFP.30-14x1.5+F FOAM	31	29.5	M14x1.5	8	-	9.5	-	11
54172-C9	SFP.30-14x1.5+F FOAM-C9	31	29.5	M14x1.5	8	-	9.5	-	11
53952	SFP.30-16x1.5+F FOAM	31	29.5	M16x1.5	10	-	9.5	-	11
53952-C9	SFP.30-16x1.5+F FOAM-C9	31	29.5	M16x1.5	10	-	9.5	-	11
53972	SFP.30-18x1.5+F FOAM	31	29.5	M18x1.5	10	-	9.5	-	12
53972-C9	SFP.30-18x1.5+F FOAM-C9	31	29.5	M18x1.5	10	-	9.5	-	12
53987	SFP.30-20x1.5+F FOAM	31	29.5	M20x1.5	12	-	9.5	-	12
53987-C9	SFP.30-20x1.5+F FOAM-C9	31	29.5	M20x1.5	12	-	9.5	-	12
53997	SFP.30-22x1.5+F FOAM	31	29.5	M22x1.5	12	-	9.5	-	13
53997-C9	SFP.30-22x1.5+F FOAM-C9	31	29.5	M22x1.5	12	-	9.5	-	13
54352	SFP.40-24x1.5+F FOAM	42	36.5	M24x1.5	18	-	11.5	-	26
54352-C9	SFP.40-24x1.5+F FOAM-C9	42	36.5	M24x1.5	18	-	11.5	-	26
54372	SFP.40-26x1.5+F FOAM	42	36.5	M26x1.5	18	-	11.5	-	17
54372-C9	SFP.40-26x1.5+F FOAM-C9	42	36.5	M26x1.5	18	-	11.5	-	17
53938	SFP.30-1/4+F FOAM	31	29.5	G 1/4	8	-	9.5	-	11
53938-C9	SFP.30-1/4+F FOAM-C9	31	29.5	G 1/4	8	-	9.5	-	11
54022	SFP.30-3/8+F FOAM	31	29.5	G 3/8	10	-	9.5	-	8
54022-C9	SFP.30-3/8+F FOAM-C9	31	29.5	G 3/8	10	-	9.5	-	12
54122	SFP.30-1/2+F FOAM	31	29.5	G 1/2	12	-	9.5	-	12
54122-C9	SFP.30-1/2+F FOAM-C9	31	29.5	G 1/2	12	-	9.5	-	12
56662	SFP.40-3/8+F FOAM	42	36.5	G 3/8	10	-	11.5	-	22
56662-C9	SFP.40-3/8+F FOAM-C9	42	36.5	G 3/8	10	-	11.5	-	22
56682	SFP.40-1/2+F FOAM	42	36.5	G 1/2	12	-	11.5	-	24
56682-C9	SFP.40-1/2+F FOAM-C9	42	36.5	G 1/2	12	-	11.5	-	24
54222	SFP.40-3/4+F FOAM	42	36.5	G 3/4	18	-	11.5	-	24
54222-C9	SFP.40-3/4+F FOAM-C9	42	36.5	G 3/4	18	-	11.5	-	24
54322	SFP.40-1+F FOAM	42	36.5	G 1	18	-	11.5	-	27
54322-C9	SFP.40-1+F FOAM-C9	42	36.5	G 1	18	-	11.5	-	27
56712	SFP.57-3/4+F FOAM	57	42	G 3/4	18	-	14	-	43
56712-C9	SFP.57-3/4+F FOAM-C9	57	42	G 3/4	18	-	14	-	43
56742	SFP.57-1+F FOAM	57	42	G 1	23	-	14	-	43
56742-C9	SFP.57-1+F FOAM-C9	57	42	G 1	23	-	14	-	43
54422	SFP.57-1¼+F FOAM	57	44	G 1 1/4	28	-	16	-	47
54422-C9	SFP.57-1¼+F FOAM-C9	57	44	G 1 1/4	28	-	16	-	47
54522	SFP.57-1½+F FOAM	57	44	G 1 1/2	28	-	16	-	47
54522-C9	SFP.57-1½+F FOAM-C9	57	44	G 1 1/2	28	-	16	-	47
54851	SFP.70-3/4+F FOAM	70	63	G 3/4	16	35	15	6	80
54851-C9	SFP.70-3/4+F FOAM-C9	70	63	G 3/4	16	35	15	6	80
54861	SFP.70-1¼+F FOAM	70	59	G 1 1/4	23	-	17	-	83
54861-C9	SFP.70-1¼+F FOAM-C9	70	59	G 1 1/4	23	-	17	-	83
54878	SFP.70-2+F FOAM	70	59	G 2	23	-	17	-	88
54878-C9	SFP.70-2+F FOAM-C9	70	59	G 2	23	-	17	-	88


Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.



SFP+F-FOAM-N


Code	Description	D	L	d	d_2	d_3	h	h_1	⚖
54152-C2-N	SFP.30-12x1.5+F FOAM-C2-N	31	29.5	M12x1.5	6	-	9.5	-	11
54152-C9-N	SFP.30-12x1.5+F FOAM-C9-N	31	29.5	M12x1.5	6	-	9.5	-	11
54172-C2-N	SFP.30-14x1.5+F FOAM-C2-N	31	29.5	M14x1.5	8	-	9.5	-	11
54172-C9-N	SFP.30-14x1.5+F FOAM-C9-N	31	29.5	M14x1.5	8	-	9.5	-	11
53952-C2-N	SFP.30-16x1.5+F FOAM-C2-N	31	29.5	M16x1.5	10	-	9.5	-	11
53952-C9-N	SFP.30-16x1.5+F FOAM-C9-N	31	29.5	M16x1.5	10	-	9.5	-	11
53972-C2-N	SFP.30-18x1.5+F FOAM-C2-N	31	29.5	M18x1.5	10	-	9.5	-	12
53972-C9-N	SFP.30-18x1.5+F FOAM-C9-N	31	29.5	M18x1.5	10	-	9.5	-	12
53987-C2-N	SFP.30-20x1.5+F FOAM-C2-N	31	29.5	M20x1.5	12	-	9.5	-	12
53987-C9-N	SFP.30-20x1.5+F FOAM-C9-N	31	29.5	M20x1.5	12	-	9.5	-	12
53997-C2-N	SFP.30-22x1.5+F FOAM-C2-N	31	29.5	M22x1.5	12	-	9.5	-	13
53997-C9-N	SFP.30-22x1.5+F FOAM-C9-N	31	29.5	M22x1.5	12	-	9.5	-	13
54352-C2-N	SFP.40-24x1.5+F FOAM-C2-N	42	36.5	M24x1.5	18	-	11.5	-	26
54352-C9-N	SFP.40-24x1.5+F FOAM-C9-N	42	36.5	M24x1.5	18	-	11.5	-	26
54372-C2-N	SFP.40-26x1.5+F FOAM-C2-N	42	36.5	M26x1.5	18	-	11.5	-	17
54372-C9-N	SFP.40-26x1.5+F FOAM-C9-N	42	36.5	M26x1.5	18	-	11.5	-	17
53938-C2-N	SFP.30-1/4+F FOAM-C2-N	31	29.5	G 1/4	8	-	9.5	-	11
53938-C9-N	SFP.30-1/4+F FOAM-C9-N	31	29.5	G 1/4	8	-	9.5	-	11
54022-C2-N	SFP.30-3/8+F FOAM-C2-N	31	29.5	G 3/8	10	-	9.5	-	12
54022-C9-N	SFP.30-3/8+F FOAM-C9-N	31	29.5	G 3/8	10	-	9.5	-	12
54122-C2-N	SFP.30-1/2+F FOAM-C2-N	31	29.5	G 1/2	12	-	9.5	-	12
54122-C9-N	SFP.30-1/2+F FOAM-C9-N	31	29.5	G 1/2	12	-	9.5	-	12
56662-C2-N	SFP.40-3/8+F FOAM-C2-N	42	36.5	G 3/8	10	-	11.5	-	22
56662-C9-N	SFP.40-3/8+F FOAM-C9-N	42	36.5	G 3/8	10	-	11.5	-	22
56682-C2-N	SFP.40-1/2+F FOAM-C2-N	42	36.5	G 1/2	12	-	11.5	-	24
56682-C9-N	SFP.40-1/2+F FOAM-C9-N	42	36.5	G 1/2	12	-	11.5	-	24
54222-C2-N	SFP.40-3/4+F FOAM-C2-N	42	36.5	G 3/4	18	-	11.5	-	24
54222-C9-N	SFP.40-3/4+F FOAM-C9-N	42	36.5	G 3/4	18	-	11.5	-	24
54322-C2-N	SFP.40-1+F FOAM-C2-N	42	36.5	G 1	18	-	11.5	-	27
54322-C9-N	SFP.40-1+F FOAM-C9-N	42	36.5	G 1	18	-	11.5	-	27
56712-C2-N	SFP.57-3/4+F FOAM-C2-N	57	42	G 3/4	18	-	14	-	43
56712-C9-N	SFP.57-3/4+F FOAM-C9-N	57	42	G 3/4	18	-	14	-	43
56742-C2-N	SFP.57-1+F FOAM-C2-N	57	42	G 1	23	-	14	-	43
56742-C9-N	SFP.57-1+F FOAM-C9-N	57	42	G 1	23	-	14	-	43
54422-C2-N	SFP.57-1¼+F FOAM-C2-N	57	44	G 1 1/4	28	-	16	-	47
54422-C9-N	SFP.57-1¼+F FOAM-C9-N	57	44	G 1 1/4	28	-	16	-	47
54522-C2-N	SFP.57-1½+F FOAM-C2-N	57	44	G 1 1/2	28	-	16	-	47
54522-C9-N	SFP.57-1½+F FOAM-C9-N	57	44	G 1 1/2	28	-	16	-	47
54851-C2-N	SFP.70-3/4+F FOAM-C2-N	70	63	G 3/4	16	35	15	6	80
54851-C9-N	SFP.70-3/4+F FOAM-C9-N	70	63	G 3/4	16	35	15	6	80
54861-C2-N	SFP.70-1¼+F FOAM-C2-N	70	59	G 1 1/4	23	-	17	-	83
54861-C9-N	SFP.70-1¼+F FOAM-C9-N	70	59	G 1 1/4	23	-	17	-	83
54878-C2-N	SFP.70-2+F FOAM-C2-N	70	59	G 2	23	-	17	-	88
54878-C9-N	SFP.70-2+F FOAM-C9-N	70	59	G 2	23	-	17	-	88

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.



SFP-BA+F

Code	Description	D	L	d_2	d_4	h	⚖
54881	SFP.70-BA+F FOAM	70	56	30	39	14	93
54881-C9	SFP.70-BA+F FOAM-C9	70	56	30	39	14	93



SFP-BA+F-N

Code	Description	D	L	d_2	d_4	h	⚖
54881-C2-N	SFP.70-BA+F FOAM-C2-N	70	56	30	39	14	93
54881-C9-N	SFP.70-BA+F FOAM-C9-N	70	56	30	39	14	93

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.