

Length details Table

Length									
mm	inches	mm	inches	mm	inches	mm	inches	mm	inches
1	0.039	57	2.244	113	4.449	169	6.654	325	12.795
2	0.079	58	2.283	114	4.488	170	6.693	330	12.992
3	0.118	59	2.323	115	4.528	171	6.732	335	13.189
4	0.157	60	2.362	116	4.567	172	6.772	340	13.386
5	0.197	61	2.402	117	4.606	173	6.811	345	13.583
6	0.236	62	2.441	118	4.646	174	6.850	350	13.780
7	0.276	63	2.480	119	4.685	175	6.890	355	13.976
8	0.315	64	2.520	120	4.724	176	6.929	360	14.173
9	0.354	65	2.559	121	4.764	177	6.969	365	14.370
10	0.394	66	2.598	122	4.803	178	7.008	370	14.567
11	0.433	67	2.638	123	4.843	179	7.047	375	14.764
12	0.472	68	2.677	124	4.882	180	7.087	380	14.961
13	0.512	69	2.717	125	4.921	181	7.126	385	15.157
14	0.551	70	2.756	126	4.961	182	7.165	390	15.354
15	0.591	71	2.795	127	5.000	183	7.205	395	15.551
16	0.630	72	2.835	128	5.039	184	7.244	400	15.748
17	0.669	73	2.874	129	5.079	185	7.283	405	15.945
18	0.709	74	2.913	130	5.118	186	7.323	410	16.142
19	0.748	75	2.953	131	5.157	187	7.362	415	16.339
20	0.787	76	2.992	132	5.197	188	7.402	420	16.535
21	0.827	77	3.031	133	5.236	189	7.441	425	16.732
22	0.866	78	3.071	134	5.276	190	7.480	430	16.929
23	0.906	79	3.110	135	5.315	191	7.520	435	17.126
24	0.945	80	3.150	136	5.354	192	7.559	440	17.323
25	0.984	81	3.189	137	5.394	193	7.598	445	17.520
26	1.024	82	3.228	138	5.433	194	7.638	450	17.717
27	1.063	83	3.268	139	5.472	195	7.677	455	17.913
28	1.102	84	3.307	140	5.512	196	7.717	460	18.110
29	1.142	85	3.346	141	5.551	197	7.756	465	18.307
30	1.181	86	3.386	142	5.591	198	7.795	470	18.504
31	1.220	87	3.425	143	5.630	199	7.835	475	18.701
32	1.260	88	3.465	144	5.669	200	7.874	480	18.898
33	1.299	89	3.504	145	5.709	205	8.071	485	19.094
34	1.339	90	3.543	146	5.748	210	8.268	490	19.291
35	1.378	91	3.583	147	5.787	215	8.465	495	19.488
36	1.417	92	3.622	148	5.827	220	8.661	500	19.685
37	1.457	93	3.661	149	5.866	225	8.858		
38	1.496	94	3.701	150	5.906	230	9.055		
39	1.535	95	3.740	151	5.945	235	9.252		
40	1.575	96	3.780	152	5.984	240	9.449		
41	1.614	97	3.819	153	6.024	245	9.646		
42	1.654	98	3.858	154	6.063	250	9.843		
43	1.693	99	3.898	155	6.102	255	10.039		
44	1.732	100	3.937	156	6.142	260	10.236		
45	1.772	101	3.976	157	6.181	265	10.433		
46	1.811	102	4.016	158	6.220	270	10.630		
47	1.850	103	4.055	159	6.260	275	10.827		
48	1.890	104	4.094	160	6.299	280	11.024		
49	1.929	105	4.134	161	6.339	285	11.220		
50	1.969	106	4.173	162	6.378	290	11.417		
51	2.008	107	4.213	163	6.417	295	11.614		
52	2.047	108	4.252	164	6.457	300	11.811		
53	2.087	109	4.291	165	6.496	305	12.008		
54	2.126	110	4.331	166	6.535	310	12.205		
55	2.165	111	4.370	167	6.575	315	12.402		
56	2.205	112	4.409	168	6.614	320	12.598		