

TL series hook clamps from Elesa

The TL series hook (toggle) clamps from Elesa include adjustable flat clamps and non-adjustable spring hook types for lighter duty use. The adjustable TLM and TLN items have turnbuckle adjustment and rigid construction to enable high tension fixing of components such as work pieces, mould components or container covers etc., whereas the TLL and TLP feature a wire loop hook which provides a degree of resilience to take up relative vibration or movement of the base components.

TL series are manufactured in zinc plated steel, nickel plated steel or stainless steel (AISI 304), while the TLML variant is both adjustable and lockable by means of small clasp lock/padlock or wire seal for which a 6mm loop is provided. Maximum loads are in the range 700N (TLP) to 3000N (TLMS).

Further information regarding Elesa products may be found at: www.elesa.co.uk or follow them on twitter: [www.twitter.com/ElesaUK](https://twitter.com/ElesaUK) – also see www.youtube.com/elesauk.



Press Box

Contact: Nigel Pritchett
Phone: +44 (0)1526 322669
E-mail: marketing@elesa.co.uk

Elesa (UK) Ltd
26 Moorlands Estate, Metherringham,
Lincolnshire, LN4 3HX, U.K.
www.elesa.co.uk – e-mail: sales@elesa.co.uk

