

Press Release

Elesa – high performing Stainless Steel Standard Components



The Elesa stainless steel program of standard components offers high performance in all areas – they are rugged and corrosion-resistant, with classic design style so as to enhance any equipment to which they are fitted.

Spoked handwheels, locking lobe knobs and hook clamps are coupled with fluid levels, levelling feet, hinges and castors in this stainless steel series designed for food processing, chemical and pharmaceutical equipment. Material grades include AISI 303, 304, 316 matched with high grade reinforced technopolymer where appropriate.

GN 949 spoked handwheels from 100mm to 200mm dia. come in plain rim format or fitted with revolving handle for easy operation. Finish is a comfortable sandblasted matt surface, fitting is by means of a reamed hole or reamed with keyway.

Lobe knobs in stainless steel are offered under the VCM-SST series with male stud or female boss fittings, they come in 40mm, 50mm and 60mm sizes.

For high performance toggle clamping Elesa offer their TLC hook clamps in AISI 304 stainless steel as typically used on quick removal panels, transit cases or other packaging systems.

Further information regarding Elesa products may be found at: www.elesa.com or follow them on twitter: [www.twitter.com/ElesaUK](https://twitter.com/ElesaUK).



Press Box

Elesa Contact: Daniel Hodson
E-mail: marketing@elesa.co.uk

ELESA (UK) Ltd.
26 Moorlands Estate – Metheringham, Lincolnshire LN4 3HX
tel. 01526 32 26 70 – sales@elesa.co.uk

www.elesa.com
STANDARD MACHINE ELEMENTS WORLDWIDE

Ref: ELES2943 – stainless steel program

Editor's PR Contact: Ian Deavin
@The Industrial Marketing Agency

E-mail: ian@theindustrialmarketingagency.co.uk
tel. 01462 850040
Mobile. 07860 218334

1941 - 2016
75
Elesa Anniversary

elesa[®]