

Elesa stainless steel industrial components for exceptionally robust service



Where the going gets tough then Elesa turns to stainless steel for their industrial components, with an extensive selection of items that parallels their steel and reinforced polyamide products. The Elesa stainless options provide extra tough in service performance that one would expect of premium stainless steel construction.

Good examples of the Elesa stainless steel approach include their MTC-S Latch Clamps with safety stop which are particularly suitable for equipment and applications with strong vibration stresses where it is required to assure the holding of the clamp engagement against accidental opening. The clamp opening is obtained by actuating the button to disengage the safety device, thus it is possible to operate with the control lever.

Their LMR levelling feet in AISI 304 and AISI 303 with rubber base provide high strength support where corrosion is a concern.

Spoked handwheels – GN 949 in cast stainless and DVC series vibration damping bushes for mounting of rotating/vibrating machines or equipment isolation – are further exemplars of the Elesa philosophy to produce high quality components for the full breadth of industry.

Further information regarding Elesa products may be found at: www.elesa.com or follow them on twitter: [www.twitter.com/ElesaUK](https://twitter.com/ElesaUK).



Press Box

Elesa Contact: Daniel Hodson
E-mail: marketing@elesa.co.uk

ELESA (UK) Ltd.
26 Moorlands Estate – Metheringham, Lincolnshire LN4 3HX
tel. 01526 32 26 70 – sales@elesa.co.uk

www.elesa.com
STANDARD MACHINE ELEMENTS WORLDWIDE

Ref: ELES3188 – stainless steel industrial components

Editor's PR Contact: Ian Deavin
@The Industrial Marketing Agency

E-mail: ian@theindustrialmarketingagency.co.uk
tel. 01462 850040
Mobile. 07860 218334

1941 - 2016
75
Elesa Anniversary

elesa®