

ELESA castors and wheels

A more complete range



The ELESA range of castors and wheels has recently been extended by introducing new items to complete the offer.

RE.C6 injected polyurethane wheel for the general public has been designed for applications requiring light loads. Thanks to its features of high wear and tearing resistance RE.C6 is suitable for use in industrial and institutional environments even in the presence of moisture and chemical agents. The good resistance to frequent cleaning cycles makes it suitable for environments where it is necessary to ensure hygiene.

RE.C7 vulcanised rubber wheel for the general public, now available with diameters from 40 mm to 80 mm, is suitable on smooth surfaces, even in presence of small obstacles.

Both series have been integrated by their respective twin wheeled version **RE.C6-G** and **RE.C7-G**, which have got higher load capacity and the same moderate dimensions.

The Elea range of castors and wheels offers complete solutions for any type of application: indoor or outdoor environments, on smooth surfaces even in presence of obstacles or chemical agents with a load capacity from 35 kg to 2,500 kg.

Numerous laboratory tests carried out according to the most strict International Standards guarantee the quality of Elea castors and wheels.

Press Box

Contact: Fabio Invernizzi
Phone: +39 039 28.111
E-mail: fabio.invernizzi@elesa.com

Elesa S.p.A.
Via Pompei, 29 – 20900 Monza – Italia
Tel. +39 039 28 111 – fax +39 039 83 63 51
www.elesa.com – e-mail: info@elesa.com

