Hinge for thin doors

Aluminium



MATERIAL

Anodised aluminium.

COLOUR

Natural, matte finish.

ROTATING PIN

AISI 304 stainless steel.

GUIDE BUSHINGS FOR PIN

Polyamide based (PA) technopolymer.

STANDARD EXECUTION

Stainless steel self-tapping screws 4.2x15.9 DIN 7982 (narrow body of the hinge) and stainless steel M5x10 semi-rounded head screws (large body of the hinge). Supplied.


FEATURES AND APPLICATIONS


The hinge is made up of two bodies with different dimensions (a narrow one and a larger one) and can be assembled for example on structures with thin frame or door. Supplied not assembled for an easy fixing.


ROTATION ANGLE (APPROXIMATE VALUE)


Max 185° (-5° and +180° being 0° the condition where the two interconnected surfaces are on the same plane).

Do not exceed the rotation angle limit so as not to prejudice the hinge mechanical performance.









Code	Description	L	В	d1	d2	L1	f	f1	Н	h1	h2	h3	b1	b2	d	44
428251	CMD-AL-45-SH-4-M5	45	43	M5	4.2	65	33	24.5	18.5	11.5	6	5.5	26	14	8	90



