


STANDARD EXECUTIONS

Aluminium, oval cross section bar.

Threaded blind holes.

Surface finish index:

- **BL**: natural colour.
- **EL**: anodised, natural colour.
- **SW**: epoxy resin coating resistant to UV rays, RAL 9005 black colour, matte finish.



GN 565

INCH

Code	Description	b	d	l	a	h	t _{min}	r	Δ
GN.92709251	GN 565-20-1/4-20-100-SW	0.79	1/4 - 20	3.94	0.51	1.93	0.39	0.51	0.21
GN.92709651	GN 565-20-1/4-20-112-SW	0.79	1/4 - 20	4.41	0.51	1.93	0.39	0.51	0.14
GN.92710251	GN 565-20-1/4-20-128-SW	0.79	1/4 - 20	5.04	0.51	2.01	0.39	0.51	0.24
GN.92710651	GN 565-20-1/4-20-160-SW	0.79	1/4 - 20	6.30	0.51	2.01	0.39	0.51	0.29
GN.92710851	GN 565-26-5/16-18-112-SW	1.02	5/16 - 18	4.41	0.67	2.17	0.47	0.67	0.37
GN.92707851	GN 565-26-5/16-18-117-SW	1.02	5/16 - 18	4.61	0.67	2.17	0.47	0.67	0.39
GN.92711051	GN 565-26-5/16-18-128-SW	1.02	5/16 - 18	5.04	0.67	2.17	0.47	0.67	0.41
GN.92711251	GN 565-26-5/16-18-160-SW	1.02	5/16 - 18	6.30	0.67	2.24	0.47	0.67	0.49
GN.92708751	GN 565-26-5/16-18-179-SW	1.02	5/16 - 18	7.05	0.67	2.24	0.47	0.67	0.55
GN.96476351	GN 565-26-5/16-18-192-SW	1.02	5/16 - 18	7.56	0.67	2.24	0.47	0.67	0.54
GN.92712251	GN 565-26-5/16-18-300-SW	1.02	5/16 - 18	11.81	0.67	2.24	0.47	0.67	0.78
GN.92712651	GN 565-26-5/16-18-400-SW	1.02	5/16 - 18	15.75	0.67	2.24	0.47	0.67	1.01
GN.92709051	GN 565-26-5/16-18-500-SW	1.02	5/16 - 18	19.69	0.67	2.24	0.47	0.67	1.18
GN.92713151	GN 565-20-1/4-20-100-EL	0.79	1/4 - 20	3.94	0.51	1.93	0.39	0.51	0.20
GN.92713251	GN 565-20-1/4-20-112-EL	0.79	1/4 - 20	4.41	0.51	1.93	0.39	0.51	0.22
GN.92713351	GN 565-20-1/4-20-128-EL	0.79	1/4 - 20	5.04	0.51	2.01	0.39	0.51	0.25
GN.92713451	GN 565-20-1/4-20-160-EL	0.79	1/4 - 20	6.30	0.51	2.01	0.39	0.51	0.28
GN.92714151	GN 565-26-5/16-18-112-EL	1.02	5/16 - 18	4.41	0.67	2.17	0.47	0.67	0.36
GN.92707751	GN 565-26-5/16-18-117-EL	1.02	5/16 - 18	4.61	0.67	2.17	0.47	0.67	0.38
GN.92714251	GN 565-26-5/16-18-128-EL	1.02	5/16 - 18	5.04	0.67	2.17	0.47	0.67	0.40
GN.92714351	GN 565-26-5/16-18-160-EL	1.02	5/16 - 18	6.30	0.67	2.24	0.47	0.67	0.43
GN.92708651	GN 565-26-5/16-18-179-EL	1.02	5/16 - 18	7.05	0.67	2.24	0.47	0.67	0.52
GN.92714451	GN 565-26-5/16-18-192-EL	1.02	5/16 - 18	7.56	0.67	2.24	0.47	0.67	0.54
GN.92714551	GN 565-26-5/16-18-300-EL	1.02	5/16 - 18	11.81	0.67	2.24	0.47	0.67	0.78
GN.92714651	GN 565-26-5/16-18-400-EL	1.02	5/16 - 18	15.75	0.67	2.24	0.47	0.67	1.04
GN.92708951	GN 565-26-5/16-18-500-EL	1.02	5/16 - 18	19.69	0.67	2.24	0.47	0.67	1.19
GN.92709151	GN 565-20-1/4-20-100-BL	0.79	1/4 - 20	3.94	0.51	1.93	0.39	0.51	0.20
GN.92709551	GN 565-20-1/4-20-112-BL	0.79	1/4 - 20	4.41	0.51	1.93	0.39	0.51	0.21
GN.92710151	GN 565-20-1/4-20-128-BL	0.79	1/4 - 20	5.04	0.51	2.01	0.39	0.51	0.24
GN.92710551	GN 565-20-1/4-20-160-BL	0.79	1/4 - 20	6.30	0.51	2.01	0.39	0.51	0.28
GN.92710751	GN 565-26-5/16-18-112-BL	1.02	5/16 - 18	4.41	0.67	2.17	0.47	0.67	0.37
GN.92707651	GN 565-26-5/16-18-117-BL	1.02	5/16 - 18	4.61	0.67	2.17	0.47	0.67	0.38
GN.92710951	GN 565-26-5/16-18-128-BL	1.02	5/16 - 18	5.04	0.67	2.17	0.47	0.67	0.39
GN.92711151	GN 565-26-5/16-18-160-BL	1.02	5/16 - 18	6.30	0.67	2.24	0.47	0.67	0.48
GN.92708551	GN 565-26-5/16-18-179-BL	1.02	5/16 - 18	7.05	0.67	2.24	0.47	0.67	0.52
GN.92711551	GN 565-26-5/16-18-192-BL	1.02	5/16 - 18	7.56	0.67	2.24	0.47	0.67	0.54
GN.92712151	GN 565-26-5/16-18-300-BL	1.02	5/16 - 18	11.81	0.67	2.24	0.47	0.67	0.77
GN.92712551	GN 565-26-5/16-18-400-BL	1.02	5/16 - 18	15.75	0.67	2.24	0.47	0.67	0.99
GN.92708851	GN 565-26-5/16-18-500-BL	1.02	5/16 - 18	19.69	0.67	2.24	0.47	0.67	1.18