



CGT metric threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560001-C3	CGT-M12x1,5-8-15-C3	cURus	VDE	cCSAus	DNV
560001-C9	CGT-M12x1,5-8-15-C9	cURus	VDE	cCSAus	DNV
560003-C3	CGT-M16x1,5-8-19-C3	cURus	VDE	--	DNV
560003-C9	CGT-M16x1,5-8-19-C9	cURus	VDE	--	DNV
560005-C3	CGT-M16x1,5-22-C3	cURus	VDE	cCSAus	DNV
560005-C9	CGT-M16x1,5-22-C9	cURus	VDE	cCSAus	DNV
560007-C3	CGT-M20x1,5-24-C3	cULus	VDE	cCSAus	DNV
560007-C9	CGT-M20x1,5-24-C9	cULus	VDE	cCSAus	DNV
560009-C3	CGT-M20x1,5-27-C3	cULus	VDE	cCSAus	DNV
560009-C9	CGT-M20x1,5-27-C9	cULus	VDE	cCSAus	DNV
560011-C3	CGT-M25x1,5-8-29-C3	cULus	VDE	cCSAus	DNV
560011-C9	CGT-M25x1,5-8-29-C9	cULus	VDE	cCSAus	DNV
560013-C3	CGT-M25x1,5-33-C3	cULus	VDE	cCSAus	DNV
560013-C9	CGT-M25x1,5-33-C9	cULus	VDE	cCSAus	DNV
560015-C3	CGT-M32x1,5-36-C3	cULus	VDE	cCSAus	DNV
560015-C9	CGT-M32x1,5-36-C9	cULus	VDE	cCSAus	DNV
560017-C3	CGT-M32x1,5-42-C3	cULus	VDE	cCSAus	DNV
560017-C9	CGT-M32x1,5-42-C9	cULus	VDE	cCSAus	DNV
560019-C3	CGT-M40x1,5-46-C3	cULus	VDE	cCSAus	DNV
560019-C9	CGT-M40x1,5-46-C9	cULus	VDE	cCSAus	DNV
560021-C3	CGT-M40x1,5-53-C3	cULus	VDE	cCSAus	DNV
560021-C9	CGT-M40x1,5-53-C9	cULus	VDE	cCSAus	DNV
560023-C3	CGT-M50x1,5-58-60-C3	cULus	VDE	cCSAus	DNV
560023-C9	CGT-M50x1,5-58-60-C9	cULus	VDE	cCSAus	DNV
560025-C3	CGT-M63x1,5-58-65-C3	cULus	VDE	cCSAus	DNV
560025-C9	CGT-M63x1,5-58-65-C9	cULus	VDE	cCSAus	DNV

CGT PG threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560051-C3	CGT-PG7-8-15-C3	cURus	--	cCSAus	DNV
560051-C9	CGT-PG7-8-15-C9	cURus	--	cCSAus	DNV
560053-C3	CGT-PG9-8-19-C3	cURus	--	cCSAus	DNV
560053-C9	CGT-PG9-8-19-C9	cURus	--	cCSAus	DNV
560055-C3	CGT-PG11-8-22-C3	cURus	--	cCSAus	DNV
560055-C9	CGT-PG11-8-22-C9	cURus	--	cCSAus	DNV
560057-C3	CGT-PG13,5-24-C3	cULus	--	cCSAus	DNV
560057-C9	CGT-PG13,5-24-C9	cULus	--	cCSAus	DNV
560059-C3	CGT-PG16-27-C3	cULus	--	cCSAus	DNV
560059-C9	CGT-PG16-27-C9	cULus	--	cCSAus	DNV
560061-C3	CGT-PG21-11-33-C3	cULus	--	cCSAus	DNV
560061-C9	CGT-PG21-11-33-C9	cULus	--	cCSAus	DNV
560063-C3	CGT-PG29-11-42-C3	cULus	--	cCSAus	DNV
560063-C9	CGT-PG29-11-42-C9	cULus	--	cCSAus	DNV
560065-C3	CGT-PG36-13-53-C3	cULus	--	cCSAus	DNV
560065-C9	CGT-PG36-13-53-C9	cULus	--	cCSAus	DNV
560067-C3	CGT-PG42-13-60-C3	cULus	--	cCSAus	DNV
560067-C9	CGT-PG42-13-60-C9	cULus	--	cCSAus	DNV
560069-C3	CGT-PG48-14-65-C3	cULus	--	cCSAus	DNV
560069-C9	CGT-PG48-14-65-C9	cULus	--	cCSAus	DNV

CGT NPT threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560071-C3	CGT-3/8 NPT-15-22-C3	cULus	--	cCSAus	DNV
560071-C9	CGT-3/8 NPT-15-22-C9	cULus	--	cCSAus	DNV
560073-C3	CGT-1/2 NPT-15-24-C3	cULus	--	cCSAus	DNV
560073-C9	CGT-1/2 NPT-15-24-C9	cULus	--	cCSAus	DNV
560075-C3	CGT-1/2 NPT-15-27-C3	cULus	--	cCSAus	DNV
560075-C9	CGT-1/2 NPT-15-27-C9	cULus	--	cCSAus	DNV
560077-C3	CGT-3/4 NPT-15-33-C3	cULus	--	cCSAus	DNV
560077-C9	CGT-3/4 NPT-15-33-C9	cULus	--	cCSAus	DNV
560079-C3	CGT-1 NPT-18-42-C3	cULus	--	cCSAus	DNV
560079-C9	CGT-1 NPT-18-42-C9	cULus	--	cCSAus	DNV

CGM metric threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560501	CGM-M12x1,5-6-14-NK	cURus	VDE	--	DNV
560503	CGM-M16x1,5-7-17-NK	cURus	VDE	--	DNV
560505	CGM-M16x1,5-7-20-NK	cURus	VDE	--	DNV
560507	CGM-M20x1,5-8-22-NK	cULus	VDE	--	DNV
560509	CGM-M25x1,5-8-24-NK	cULus	VDE	--	DNV
560511	CGM-M25x1,5-8-27-NK	cULus	VDE	--	DNV
560513	CGM-M32x1,5-9-30-NK	cULus	VDE	--	DNV
560515	CGM-M32x1,5-8-34-NK	cULus	VDE	--	DNV
560517	CGM-M40x1,5-9-40-NK	cULus	VDE	--	DNV
560519	CGM-M40x1,5-9-43-NK	cULus	VDE	--	DNV
560521	CGM-M50x1,5-9-50-NK	cULus	VDE	--	DNV
560523	CGM-M50x1,5-9-58-NK	cULus	VDE	--	DNV
560525	CGM-M63x1,5-14-64-NK	cULus	VDE	--	DNV

CGM-SST metric threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560601	CGM-M12x1,5-6-14-SST	cURus	VDE	--	DNV
560603	CGM-M16x1,5-7-17-SST	cURus	VDE	--	DNV
560605	CGM-M16x1,5-7-22-SST	cULus	VDE	--	DNV
560607	CGM-M20x1,5-8-22-SST	cULus	VDE	--	DNV
560609	CGM-M25x1,5-8-24-SST	cULus	VDE	--	DNV
560611	CGM-M25x1,5-8-27-SST	cULus	VDE	--	DNV
560613	CGM-M32x1,5-9-30-SST	cULus	VDE	--	DNV
560615	CGM-M32x1,5-8-36-SST	cULus	VDE	--	DNV
560617	CGM-M40x1,5-9-41-SST	cULus	VDE	--	DNV
560619	CGM-M40x1,5-9-46-SST	cULus	VDE	--	DNV
560621	CGM-M50x1,5-9-50-SST	cULus	VDE	--	DNV
560623	CGM-M50x1,5-9-60-SST	cULus	VDE	--	DNV
560625	CGM-M63x1,5-14-65-SST	cULus	VDE	--	DNV

CGM PG threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560531	CGM-PG7-6-14-NK	cURus	--	--	DNV
560533	CGM-PG9-6-17-NK	cURus	--	--	DNV
560535	CGM-PG11-6-20-NK	cURus	--	--	DNV
560537	CGM-PG13,5-6,5-22-NK	cULus	--	--	DNV
560539	CGM-PG16-6,5-24-NK	cULus	--	--	DNV
560541	CGM-PG21-7,2-30-NK	cULus	--	--	DNV
560543	CGM-PG29-8-40-NK	cULus	--	--	DNV
560545	CGM-PG36-9-50-NK	cULus	--	--	DNV
560547	CGM-PG48-14-64-NK	cULus	--	--	DNV

CGM-SST PG threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560631	CGM-PG7-6-14-SST	cURus	--	--	DNV
560633	CGM-PG9-6-19-SST	cURus	--	--	DNV
560635	CGM-PG11-6-22-SST	cULus	--	--	DNV
560637	CGM-PG13,5-6,5-22-SST	cULus	--	--	DNV
560639	CGM-PG16-6,5-24-SST	cULus	--	--	DNV
560641	CGM-PG21-7,2-30-SST	cULus	--	--	DNV
560643	CGM-PG29-8-41-SST	cULus	--	--	DNV
560645	CGM-PG36-9-50-SST	cULus	--	--	DNV
560647	CGM-PG48-14-65-SST	cULus	--	--	DNV

CGM NPT threadings					
Code	Description	Certifications			
		UL	VDE	CSA	DNV
560549	CGM-3/8-NPT-11,5-17-NK	cURus	--	--	DNV
560551	CGM-1/2-NPT-13-22-NK	cULus	--	--	DNV
560553	CGM-1/2-NPT-13-24-NK	cULus	--	--	DNV
560555	CGM-3/4-NPT-13-30-NK	cULus	--	--	DNV