UC-RF antenna extensions

with SMA-RP connector

CABLE
Shielded cable with PVC sheath, bend radius in fixed position ≥ 50 mm.

CONNECTORS
Male and female SMA-RP connectors.

APPLICATIONS
If the extension is used as a spare part in an existing equipment, please contact the Elesa technical service to check its compatibility.

SPECIAL EXECUTIONS ON REQUEST
Extensions with cables in different lengths.



Mechanical and electrical characteristics	
Impedance	50 Ohm
Working temperature	-40 °C ÷ 70 °C



Code	Description	L+/- 50	d±0.5	⚖
CE.99263	FC-UC-1.0-R	1000	3	48
CE.99265	FC-UC-2.5-R	2500	5	106
CE.99267	FC-UC-5.0-R	5000	5	208
CE.99269	FC-UC-10.0-R	10000	5	206

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.