Linear guide rail

Round profile R7, technopolymer, stainless steel

INOX STAINLESS STEEL | RoHS | HMWPE | +90° -20°

GUIDE PROFILE
Polyethylene based (HMWPE) technopolymer, natural colour.

BRACKET
AISI 304 stainless steel


FEATURES AND APPLICATIONS
GLT guide rail for the side guide of products with a good stability on conveyor belts (Fig.1), without leaving traces on the containers.
High molecular weight polyethylene (HMWPE) has a high wear resistance; it is particularly suitable for high-speed movements due to its low coefficient of friction.
Supplied in bars of 1500 or 3000 mm length.


SPECIAL EXECUTIONS ON REQUEST
Guide rails in blue colour RAL 5005.


ACCESSORIES ON REQUEST
- Guide rail clamps MPG-T, MPG-2T, MPG-T-S.
- End brackets for linear guide rails TGLT.



Fig.1







INOX STAINLESS STEEL

Code	Description	L	⚖
419197	GLT-14R7-3000	3000	2070
419196	GLT-14R7-1500	1500	1038

11/2025

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.