GN 287 | Pivoting connecting clamps

Aluminium


RoHS


MATERIAL
Aluminium, matte finish.
AISI 304 stainless steel screws and nuts.


STANDARD EXECUTIONS
Surface finish index:
- **BL**: natural colour.
- **SW**: epoxy resin coating resistant to UV rays, RAL 9005 black colour.

FEATURES AND APPLICATIONS
The assembly hole of GN 287 connecting clamps allows an excellent match with tubes GN 990 (see page 1368).
GN 287 connecting clamps are an assembly of connecting clamps GN 275 (see page 1346) and GN 277 (see page 1347).
The clamping screws d3 may be replaced by clamping kits GN 911 (see page 1372).

SPECIAL EXECUTIONS ON REQUEST
Different combinations of holes d1/d2.







GN 287-BL

Code	Description	b	d1	d2	d3	k1	k2	l1	l2	l3	m1	m2	d3 Clamping kit	⚖
GN.64611	GN 287-B12-B12-2-BL	25	12	12	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	145
GN.64631	GN 287-B14-B14-2-BL	25	14	14	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	130
GN.64651	GN 287-B16-B16-2-BL	25	16	16	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	130
GN.64671	GN 287-B18-B18-2-BL	25	18	18	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	130

GN 287-SW

Code	Description	b	d1	d2	d3	k1	k2	l1	l2	l3	m1	m2	d3 Clamping kit	⚖
GN.64616	GN 287-B12-B12-2-SW	25	12	12	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	145
GN.64636	GN 287-B14-B14-2-SW	25	14	14	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	130
GN.64656	GN 287-B16-B16-2-SW	25	16	16	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	130
GN.64676	GN 287-B18-B18-2-SW	25	18	18	M6	25	25	100	34.5	25	29.5	48.5	GN 911-M6-22	130

elesa 11/2021
Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.
Ganter Norm