

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

**SPECIFICATION**



Brass **MS**  
Plain  
AISI 316L stainless steel **A4**  
Plain

**FEATURES AND APPLICATIONS**

Mounting nuts GN 7430 are used, for example, to fasten breather elements, oil level sight glasses or threaded plugs when the wall is too thin for inserting a thread or this is to be avoided for manufacturing simplification.

The sufficiently large hexagonal profile is chamfered on one side only, which increases the bearing surface and the thread length.

The stainless steel versions can be secured inside the housing by spot welds to facilitate assembly, they are generally suitable for applications with aggressive environmental conditions.



**GN 7430-MS**

Code	Description	d1	d2 +0.3	b	e	s	$\frac{\Delta}{\Delta}$
GN.32343	GN 7430-G1/4-MS	G 1/4	13.2	3	17.5	16	1
GN.32353	GN 7430-G3/8-MS	G 3/8	16.7	3	23	21	2
GN.32342	GN 7430-G1/2-MS	G 1/2	21	4	26	24	6
GN.32351	GN 7430-G3/4-MS	G 3/4	26.5	4	32.5	30	8
GN.32348	GN 7430-G1-MS	G 1	33.3	5	44.5	41	25
GN.32349	GN 7430-G2-MS	G 2	59.7	6	72	65	45
GN.32346	GN 7430-G1 1/4-MS	G 1 1/4	42	5	50.5	46	32
GN.32344	GN 7430-G1 1/2-MS	G 1 1/2	47.9	6	61	55	43
GN.32361	GN 7430-M12X1.5-MS	M12x1.5	12	3	17.5	16	1
GN.32362	GN 7430-M14X1.5-MS	M14x1.5	14	3	19.5	18	2
GN.32364	GN 7430-M16X1.5-MS	M16x1.5	16	3	23	21	4
GN.32366	GN 7430-M20X1.5-MS	M20x1.5	20	4	26	24	6
GN.32368	GN 7430-M26X1.5-MS	M26x1.5	26	4	32.5	30	9
GN.32369	GN 7430-M27X1.5-MS	M27x1.5	27	4	34.5	32	11
GN.32371	GN 7430-M33X1.5-MS	M33x1.5	33	5	44.5	41	25
GN.32372	GN 7430-M40X1.5-MS	M40x1.5	40	5	50.5	46	27
GN.32374	GN 7430-M42X1.5-MS	M42x1.5	42	5	54.5	50	32

**GN 7430-A4**

Code	Description	d1	d2 +0.3	b	e	s	$\frac{\Delta}{\Delta}$
GN.32352	GN 7430-G3/8-A4	G 3/8	16.7	3	23	21	4
GN.32341	GN 7430-G1/2-A4	G 1/2	21	4	26	24	11
GN.32350	GN 7430-G3/4-A4	G 3/4	26.5	4	32.5	30	17
GN.32347	GN 7430-G1-A4	G 1	33.3	5	44.5	41	24
GN.32345	GN 7430-G1 1/4-A4	G 1 1/4	42	5	50.5	46	27
GN.32363	GN 7430-M16X1.5-A4	M16x1.5	16	3	23	21	4
GN.32365	GN 7430-M20X1.5-A4	M20x1.5	20	4	26	24	13
GN.32367	GN 7430-M26X1.5-A4	M26x1.5	26	4	32.5	30	17
GN.32370	GN 7430-M33X1.5-A4	M33x1.5	33	5	44.5	41	24
GN.32373	GN 7430-M42X1.5-A4	M42x1.5	42	5	54.5	50	30

Accessories for hydraulic systems