

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

MATERIAL

Zinc-plated steel, class 8.8.


FEATURES AND APPLICATIONS

Hexagon head screws (ISO 4014/4017) for fastening the top plate to the half clamps.

ACCESSORIES

For the assembly kit DCK-S, DCK-H and DCK-D.

- DCE-S: standard series tube clamps.
- DCE-H: heavy-duty series tube clamps.
- DCE-D: double series tube clamps.
- DCE-PU: top plate.
- DCE-WA: flat washer.
- DCE-GU: mounting guide.
- DCE-NTG: nut for mounting guide.



METRIC

| Code | Description | d | l | l1 | For tube clamps | △ |
|--------|--------------------|------|-----|----|-----------------|-----|
| 570121 | DCE-SRE-M6X30-ZN | M 6 | 30 | 18 | DCE-S - DCE-D | 9 |
| 570123 | DCE-SRE-M6X35-ZN | M 6 | 35 | 18 | DCE-S - DCE-D | 10 |
| 570125 | DCE-SRE-M6X40-ZN | M 6 | 40 | 18 | DCE-S | 11 |
| 570127 | DCE-SRE-M6X45-ZN | M 6 | 45 | 18 | DCE-S | 12 |
| 570129 | DCE-SRE-M6X60-ZN | M 6 | 60 | 18 | DCE-S | 15 |
| 570131 | DCE-SRE-M6X70-ZN | M 6 | 70 | 18 | DCE-S | 17 |
| 570141 | DCE-SRE-M8X30-ZN | M 8 | 30 | 30 | DCE-D | 15 |
| 570143 | DCE-SRE-M8X35-ZN | M 8 | 35 | 22 | DCE-D | 17 |
| 570145 | DCE-SRE-M8X40-ZN | M 8 | 40 | 22 | DCE-D | 19 |
| 570147 | DCE-SRE-M8X45-ZN | M 8 | 45 | 22 | DCE-D | 20 |
| 570149 | DCE-SRE-M8X50-ZN | M 8 | 50 | 22 | DCE-D | 22 |
| 570151 | DCE-SRE-M8X55-ZN | M 8 | 55 | 22 | DCE-D | 24 |
| 570153 | DCE-SRE-M8X60-ZN | M 8 | 60 | 22 | DCE-D | 27 |
| 570161 | DCE-SRE-M10X45-ZN | M 10 | 45 | 26 | DCE-H | 36 |
| 570163 | DCE-SRE-M10X60-ZN | M 10 | 60 | 26 | DCE-H | 45 |
| 570165 | DCE-SRE-M10X70-ZN | M 10 | 70 | 26 | DCE-H | 52 |
| 570171 | DCE-SRE-M12X100-ZN | M 12 | 100 | 30 | DCE-H | 98 |
| 570173 | DCE-SRE-M16X130-ZN | M 16 | 130 | 44 | DCE-H | 228 |

Accessories for hydraulic systems