



PROFILE

Zinc-plated steel.



PINS SUPPORT

Glass-fibre reinforced acetal resin based (PA) technopolymer, black colour.



PINS

AISI 304 stainless steel.



ROLLERS

Shaped with cylindrical contact area, in acetal resin technopolymer, white colour.



STANDARD EXECUTIONS

- **GLD-1-AZ:** one row of rollers.
- **GLD-2-AZ:** two rows of rollers.
- **GLD-3-AZ:** three rows of rollers.
- **GLD-4-AZ:** four rows of rollers.



FEATURES AND APPLICATIONS

The GLD-AZ side guides are particularly solid self-supporting structures, suitable for handling products of significant weight and size (e.g. pallets).



The shaped rollers are particularly suitable for glass product guides, as in the event of accidental breakages they facilitate the expulsion of debris.



SPECIAL EXECUTIONS ON REQUEST

Roller side guides with zinc-plated steel profile, length 3129 mm.




ACCESSORIES ON REQUEST


- MPG-R-AZ: guide rail clamps
- MPG-P: fixing pin (419513 MPG-P16-M10x17).
- SPF: guide rail brackets for linear positioning.
- SPR: guide rail brackets for linear and corner positioning.
- SPR.V: guide rail brackets for linear and corner positioning.




GLD-1-AZ




GLD-2-AZ








GLD-3-AZ



GLD-4-AZ





Conversion Table 1 mm = 0.039 inch	
mm	inch
47.4	1.85
73.4	2.86
100.4	3.92
126.9	4.95

GLD-1-AZ

Code	Description	L	B	l1	l2	l3	Mounting brackets	⚖
419301	GLD-1-AZ-RT-47-1041	47.4	1041	38.5	28	34	MPG-R-AZ-1	2660
419303	GLD-1-AZ-RT-47-2085	47.4	2085	38.5	28	34	MPG-R-AZ-1	5320

GLD-2-AZ

Code	Description	L	B	l1	l2	l3	Mounting brackets	⚖
419311	GLD-2-AZ-RT-73-1041	73.4	1041	64.5	54	60	MPG-R-AZ-2	3940
419313	GLD-2-AZ-RT-73-2085	73.4	2085	64.5	54	60	MPG-R-AZ-2	7880

GLD-3-AZ

Code	Description	L	B	l1	l2	l3	Mounting brackets	⚖
419321	GLD-3-AZ-RT-100-1041	100.4	1041	91.5	81	87	MPG-R-AZ-3	5188
419323	GLD-3-AZ-RT-100-2085	100.4	2085	91.5	81	87	MPG-R-AZ-3	10376

GLD-4-AZ

Code	Description	L	B	l1	l2	l3	Mounting brackets	⚖
419331	GLD-4-AZ-RT-127-1041	126.9	1041	118	107.5	113.5	MPG-R-AZ-4	6420
419333	GLD-4-AZ-RT-127-2085	126.9	2085	118	107.5	113.5	MPG-R-AZ-4	12840