

**MATERIAL**


Polyamide based (PA) technopolymer, natural colour.

**FEATURES AND APPLICATIONS**

The wing nut screw allows the screw and washer to be combined into a single component and requires no tools for tightening.

It is made entirely from insulating material that is resistant to corrosion and chemicals. It is suitable for applications in industry, aeronautics and electronics, and in all cases where weight reduction is required.

The product is tested for mechanical and dimensional performance. Slight colour variations are perfectly normal and do not affect the quality of the product.



METRIC

Code	Description	d	d1	l	s	h	Maximum tightening torque [Nm]	⚖️
504201	SRA-21-M5X16-TP-N	M5	21	16	8.5	12.5	0.25	1
504202	SRA-21-M5X20-TP-N	M5	21	20	8.5	12.5	0.25	1
504203	SRA-21-M5X25-TP-N	M5	21	25	8.5	12.5	0.25	1
504204	SRA-21-M5X30-TP-N	M5	21	30	8.5	12.5	0.25	1
504205	SRA-21-M5X40-TP-N	M5	21	40	8.5	12.5	0.25	1
504206	SRA-21-M5X50-TP-N	M5	21	50	8.5	12.5	0.25	1.5
504211	SRA-21-M6X16-TP-N	M6	21	16	8.5	12.5	0.5	1
504212	SRA-21-M6X20-TP-N	M6	21	20	8.5	12.5	0.5	1.5
504213	SRA-21-M6X25-TP-N	M6	21	25	8.5	12.5	0.5	1.5
504214	SRA-21-M6X30-TP-N	M6	21	30	8.5	12.5	0.5	1.5
504215	SRA-21-M6X40-TP-N	M6	21	40	8.5	12.5	0.5	1.5
504216	SRA-21-M6X50-TP-N	M6	21	50	8.5	12.5	0.5	2
504221	SRA-21-M8X20-TP-N	M8	21	20	8.5	12.5	1.9	2
504222	SRA-21-M8X25-TP-N	M8	21	25	8.5	12.5	1.9	2
504223	SRA-21-M8X30-TP-N	M8	21	30	8.5	12.5	1.9	2.5
504224	SRA-21-M8X40-TP-N	M8	21	40	8.5	12.5	1.9	3
504225	SRA-21-M8X50-TP-N	M8	21	50	8.5	12.5	1.9	3.5
504231	SRA-21-M10X20-TP-N	M10	21	20	8.5	12.5	3	3.5
504232	SRA-21-M10X25-TP-N	M10	21	25	8.5	12.5	3	4
504233	SRA-21-M10X30-TP-N	M10	21	30	8.5	12.5	3	5
504234	SRA-21-M10X40-TP-N	M10	21	40	8.5	12.5	3	5
504235	SRA-21-M10X50-TP-N	M10	21	50	8.5	12.5	3	5.5
504236	SRA-21-M10X60-TP-N	M10	21	60	8.5	12.5	3	6
504241	SRA-21-M12X20-TP-N	M12	21	20	8.5	12.5	4.7	5
504242	SRA-21-M12X30-TP-N	M12	21	30	8.5	12.5	4.7	6
504243	SRA-21-M12X40-TP-N	M12	21	40	8.5	12.5	4.7	7
504244	SRA-21-M12X50-TP-N	M12	21	50	8.5	12.5	4.7	8
504245	SRA-21-M12X60-TP-N	M12	21	60	8.5	12.5	4.7	9
504246	SRA-21-M12X80-TP-N	M12	21	80	8.5	12.5	4.7	9.5