RoHS PA

PROFILE
Zinc-plated steel.

PINS SUPPORT
Glass-fibre reinforced polyamide based (PA) technopolymer, black colour.

PINS
AISI 304 stainless steel.

ROLLERS
Shaped with cylindrical contact area, in acetal resin technopolymer, white colour.

STANDARD EXECUTIONS
- **GLD-1-AZ**: one row of rollers.
- **GLD-2-AZ**: two rows of rollers.
- **GLD-3-AZ**: three rows of rollers.
- **GLD-4-AZ**: four rows of rollers.


FEATURES AND APPLICATIONS
The GLD-AZ side guides are particularly solid self-supporting structures, suitable for handling products of significant weight and size (e.g. pallets).
The shaped rollers are particularly suitable for glass product guides, as in the event of accidental breakages they facilitate the expulsion of debris.

SPECIAL EXECUTIONS ON REQUEST
Roller side guides with zinc-plated steel profile, length 3129 mm.


ACCESSORIES ON REQUEST
- MPG-R-AZ: guide rail clamps
- MPG-P: fixing pin (419513 MPG-P16-M10x17).
- SPF.: guide rail brackets for linear positioning.
- SPR.: guide rail brackets for linear and corner positioning.
- SPR.V: guide rail brackets for linear and corner positioning.




GLD-1-AZ




GLD-2-AZ



GLD-3-AZ




GLD-4-AZ




elesa 11/2026


Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.




GLD-1-AZ




GLD-2-AZ



GLD-3-AZ



GLD-4-AZ



GLD-1-AZ

Code	Description	L	B	l_1	l_2	l_3	Mounting brackets	⚖
419301	GLD-1-AZ-RT-47-1041	47.4	1041	38.5	28	34	MPG-R-AZ-1	2770
419303	GLD-1-AZ-RT-47-2085	47.4	2085	38.5	28	34	MPG-R-AZ-1	5540

GLD-2-AZ

Code	Description	L	B	l_1	l_2	l_3	Mounting brackets	⚖
419311	GLD-2-AZ-RT-73-1041	73.4	1041	64.5	54	60	MPG-R-AZ-2	3960
419313	GLD-2-AZ-RT-73-2085	73.4	2085	64.5	54	60	MPG-R-AZ-2	7920

GLD-3-AZ

Code	Description	L	B	l_1	l_2	l_3	Mounting brackets	⚖
419321	GLD-3-AZ-RT-100-1041	100.4	1041	91.5	81	87	MPG-R-AZ-3	5370
419323	GLD-3-AZ-RT-100-2085	100.4	2085	91.5	81	87	MPG-R-AZ-3	10740

GLD-4-AZ

Code	Description	L	B	l_1	l_2	l_3	Mounting brackets	⚖
419331	GLD-4-AZ-RT-127-1041	126.9	1041	118	107.5	113.5	MPG-R-AZ-4	6600
419333	GLD-4-AZ-RT-127-2085	126.9	2085	118	107.5	113.5	MPG-R-AZ-4	13300

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.