

Hinges



Material

Glass-fibre reinforced polyamide based (PA) SUPER-technopolymer. Resistant to solvents, oils, greases and other chemical agents.

Colour

- CFM.: black, matte finish.
- CFM-CLEAN: white similar to RAL 9002, matte finish.

Rotating pin

AISI 303 stainless steel.

Standard executions


- **CFM-p**: nickel-plated steel threaded studs.
- **CFM-SH**: pass-through holes for countersunk head screws.
- **CFM-CH**: pass-through holes for cylindrical head screws with washer type UNI 6592.
- **CFM-p-SH**: nickel-plated steel threaded studs and pass-through holes for countersunk head screws.
- **CFM-p-CH**: nickel-plated steel threaded studs and pass-through holes for cylindrical head screws with UNI 6592 washer.
- **CFM.60-SL-CH**: pass-through slotted hole for shorted cylindrical head screws UNI 9327 which allow adjustment during clamping.

Rotation angle (approximate value)

Max 270° (-90° and +180° being 0° the condition where the two interconnected surfaces are on the same plane).

Do not exceed the rotation angle limit so as not to prejudice the hinge mechanical performance.

To choose the convenient type and the right number of hinges for your application, see the Guidelines




Resistance tests	AXIAL STRESS	RADIAL STRESS	90° ANGLED STRESS
	Max limit static load	Max limit static load	Max limit static load
Description	Sa [N]	Sr [N]	S90 [N]
CFM.30 SH-4	1400	1700	1000
CFM.30 CH-4	1300	1700	850
CFM.40 p-M5x12	2000	1900	1000
CFM.40 SH-5	1900	1900	1280
CFM.40 CH-5	1900	1600	1000
CFM.40 p-M5x12-SH-5	1900	1900	1000
CFM.40 p-M5x12-CH-5	1900	1600	1000
CFM.50 p-M6x12	2340	2560	2100
CFM.50 SH-6	2630	2400	1720
CFM.50 p-M6x12-SH-6	800	1600	1000
CFM.50 p-M6x12-CH-6	600	1500	1000
CFM.50 CH-6	2860	2410	1360
CFM.50 p-M6x12-SH-6	2340	2400	1720
CFM.50 p-M6x12-CH-6	2340	2410	1360
CFM.60 p-M8x14.5	3000	3940	2130
CFM.60 SH-8	3320	2960	3070
CFM.60 CH-8	3440	2810	2170
CFM.60 p-M8x14.5-SH-8	3000	2960	2130
CFM.60 p-M8x14.5-CH-8	3000	2810	2130
CFM.60-45-SH-6	2920	3010	1310
CFM.60-SL-CH-6	960	1200	1360


The max static load is the value above which the material may break thus prejudicing the hinge functionality use. Obviously, a suitable factor, according to the importance and the safety level of the specific application must be applied to this value.




CFM-p



CFM-SH



CFM-CH




Conversion Table

1 mm = 0.039 inch


L

mm	inch
30	1.18
40	1.57
50	1.97
60	2.36


CFM-p-SH



CFM-p-CH



CFM.60-SL-CH




Conversion Table

1 mm = 0.039 inch

d5


mm	inch
8.5	0.33
10.5	0.41
12.5	0.49
16.5	0.65



CFM.50-63 SH

CFM.50-76 SH

CFM.60-SL-CH



Conversion Table

1 mm = 0.039 inch

b3

mm	inch
10.5	0.41

CFM.

Code	Description	L	B	d2	l	f _{±0.25}	f1 _{±0.25}	f2	f3	H	h1	h2	h3	b1	b2	d	d3	d4	d5	C [Nm] p#	C [Nm] SH/CH#	⚖		
425411	CFM.30-SH-4	30	30	-	-	18	18	-	-	7	4	3.5	-	10.5	10.5	2.5	4.5	8.5	-	-	3	11		
425412	CFM.30-CH-4	30	30	-	-	18	18	-	-	7	4	3.5	1.3	10.5	10.5	2.5	4.5	-	8.5	-	-	3	11	
425521	CFM.40-p-M5x12	40	40	M5	12	25	25	-	-	9	5.5	5	-	14	14	4	-	-	-	-	5	-	26	
425511	CFM.40-SH-5	40	40	-	-	25	25	-	-	9	5.5	5	-	14	14	4	5.5	10.5	-	-	-	3	14	
425512	CFM.40-CH-5	40	40	-	-	25	25	-	-	9	5.5	5	1.7	14	14	4	5.5	-	10.5	-	-	5	14	
425531	CFM.40-p-M5x12-SH-5	40	40	M5	12	25	25	-	-	9	5.5	5	-	14	14	4	5.5	10.5	-	-	5	3	20	
425532	CFM.40-p-M5x12-CH-5	40	40	M5	12	25	25	-	-	9	5.5	5	1.7	14	14	4	5.5	-	10.5	5	5	5	20	
425621	CFM.50-p-M6x12	50	50	M6	12	30	30	-	-	11.5	6.5	6	-	18	18	6	-	-	-	-	5	-	50	
425611	CFM.50-SH-6	50	50	-	-	30	30	-	-	11.5	6.5	6	-	18	18	6	6.5	12.5	-	-	-	5	30	
425851	CFM.50-63-SH-6	50	63	-	-	30	43	15	28	11.5	6.5	6	-	18	31	6	6.5	12.5	-	-	-	5	37	
425856	CFM.50-76-SH-6	50	76	-	-	30	56	28	28	11.5	6.5	6	-	31	31	6	6.5	12.5	-	-	-	5	42	
425612	CFM.50-CH-6	50	50	-	-	30	30	-	-	11.5	6.5	6	3	18	18	6	6.5	-	12.5	-	-	5	30	
425631	CFM.50-p-M6x12-SH-6	50	50	M6	12	30	30	-	-	11.5	6.5	6	-	18	18	6	6.5	12.5	-	-	5	5	40	
425632	CFM.50-p-M6x12-CH-6	50	50	M6	12	30	30	-	-	11.5	6.5	6	3	18	18	6	6.5	-	12.5	5	5	5	40	
425721	CFM.60-p-M8x14.5	60	60	M8	14.5	36	36	-	-	15	8.5	8	-	21	21	8	-	-	-	-	5	-	101	
425711	CFM.60-SH-8	60	60	-	-	36	36	-	-	15	8.5	8	-	21	21	8	8.5	16.5	-	-	-	5	57	
425712	CFM.60-CH-8	60	60	-	-	36	36	-	-	15	8.5	8	4	21	21	8	8.5	-	16.5	-	-	5	57	
425731	CFM.60-p-M8x14.5-SH-8	60	60	M8	14.5	36	36	-	-	15	8.5	8	-	21	21	8	8.5	16.5	-	-	5	5	79	
425732	CFM.60-p-M8x14.5-CH-8	60	60	M8	14.5	36	36	-	-	15	8.5	8	4	21	21	8	8.5	-	16.5	5	5	5	79	
425812	CFM.60-45-SH-6	60	70	-	-	34	45	-	-	14.5	8	7.5	-	26	26	8	6.5	12.5	-	-	-	5	62	
425822	CFM.60-SL-CH-6	60	70	-	-	34	40	-	-	14.5	8	7.5	4	26	26	8	6.5	10.5	-	-	-	4	61	

CFM-CLEAN

Code	Description	L	B	f _{±0.25}	f1 _{±0.25}	H	h1	h2	b1	b2	d	d3	d4	C# [Nm]	⚖
425441	CFM.30 SH-4-CLEAN	30	30	18	18	7	4	3.5	10.5	10.5	2.5	4.5	8.5	3	11
425541	CFM.40 SH-5-CLEAN	40	40	25	25	9	5.5	5	14	14	4	5.5	10.5	3	14
425641	CFM.50 SH-6-CLEAN	50	50	30	30	11.5	6.5	6	18	18	6	6.5	12.5	5	30
425741	CFM.60 SH-8-CLEAN	60	60	36	36	15	8.5	8	21	21	8	8.5	16.5	5	57

Suggested tightening torque for assembly screws.