

MATERIAL

Polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTIONS

- **BT-HP-p**: zinc-plated steel threaded stud, chamfered flat end UNI EN ISO 4753 : 2012 (see Technical data on page A-11).
- **BT-HP-SST-p**: AISI 304 stainless steel threaded stud, chamfered flat end UNI EN ISO 4753 : 2012 (see Technical data on page A-11).


FEATURES AND APPLICATIONS

The retained fluted knobs are used to secure blanking plates, covers, or other items without the risk of loss.

This is made possible by the non-threaded part of the stem, which allows the knob to remain anchored (retained) to the machinery.



ELESA Original design



BT-HP-p

| Code | Description      | D  | L  | d1 | d2 | d3 ±0.1 | d4  | l1 | l2 | l3 | h | a1     | a2      | a3      | △  |
|------|------------------|----|----|----|----|---------|-----|----|----|----|---|--------|---------|---------|----|
| 5351 | BT-HP.25-p-M6x22 | 25 | 19 | M6 | 16 | 4.7     | 6.5 | 22 | 8  | 3  | 8 | 5 + 8  | 10 + 16 | 15 + 24 | 13 |
| 5356 | BT-HP.25-p-M6x32 | 25 | 19 | M6 | 16 | 4.7     | 6.5 | 32 | 8  | 3  | 8 | 5 + 8  | 10 + 16 | 15 + 24 | 15 |
| 5361 | BT-HP.25-p-M8x30 | 25 | 19 | M8 | 16 | 6.5     | 8.5 | 30 | 10 | 4  | 8 | 7 + 10 | 14 + 20 | 21 + 30 | 18 |
| 5366 | BT-HP.25-p-M8x40 | 25 | 19 | M8 | 16 | 6.5     | 8.5 | 40 | 10 | 4  | 8 | 7 + 10 | 14 + 20 | 21 + 30 | 23 |
| 5369 | BT-HP.32-p-M6x18 | 32 | 23 | M6 | 17 | 4.7     | 6.5 | 18 | 8  | 3  | 9 | 5 + 8  | 10 + 16 | 15 + 24 | 15 |
| 5371 | BT-HP.32-p-M6x22 | 32 | 23 | M6 | 17 | 4.7     | 6.5 | 22 | 8  | 3  | 9 | 5 + 8  | 10 + 16 | 15 + 24 | 16 |
| 5376 | BT-HP.32-p-M6x32 | 32 | 23 | M6 | 17 | 4.7     | 6.5 | 32 | 8  | 3  | 9 | 5 + 8  | 10 + 16 | 15 + 24 | 18 |
| 5381 | BT-HP.32-p-M8x30 | 32 | 23 | M8 | 17 | 6.5     | 8.5 | 30 | 10 | 4  | 9 | 7 + 10 | 14 + 20 | 21 + 30 | 22 |
| 5386 | BT-HP.32-p-M8x40 | 32 | 23 | M8 | 17 | 6.5     | 8.5 | 40 | 10 | 4  | 9 | 7 + 10 | 14 + 20 | 21 + 30 | 27 |

BT-HP-SST-p

| Code   | Description          | D  | L  | d1 | d2 | d3 ±0.1 | d4  | l1 | l2 | l3 | h | a1     | a2      | a3      | △  |
|--------|----------------------|----|----|----|----|---------|-----|----|----|----|---|--------|---------|---------|----|
| 105351 | BT-HP.25-SST-p-M6x22 | 25 | 19 | M6 | 16 | 4.7     | 6.5 | 22 | 8  | 3  | 8 | 5 + 8  | 10 + 16 | 15 + 24 | 13 |
| 105356 | BT-HP.25-SST-p-M6x32 | 25 | 19 | M6 | 16 | 4.7     | 6.5 | 32 | 8  | 3  | 8 | 5 + 8  | 10 + 16 | 15 + 24 | 15 |
| 105361 | BT-HP.25-SST-p-M8x30 | 25 | 19 | M8 | 16 | 6.5     | 8.5 | 30 | 10 | 4  | 8 | 7 + 10 | 14 + 20 | 21 + 30 | 18 |
| 105366 | BT-HP.25-SST-p-M8x40 | 25 | 19 | M8 | 16 | 6.5     | 8.5 | 40 | 10 | 4  | 8 | 7 + 10 | 14 + 20 | 21 + 30 | 23 |
| 105371 | BT-HP.32-SST-p-M6x22 | 32 | 23 | M6 | 17 | 4.7     | 6.5 | 22 | 8  | 3  | 9 | 5 + 8  | 10 + 16 | 15 + 24 | 16 |
| 105376 | BT-HP.32-SST-p-M6x32 | 32 | 23 | M6 | 17 | 4.7     | 6.5 | 32 | 8  | 3  | 9 | 5 + 8  | 10 + 16 | 15 + 24 | 18 |
| 105381 | BT-HP.32-SST-p-M8x30 | 32 | 23 | M8 | 17 | 6.5     | 8.5 | 30 | 10 | 4  | 9 | 7 + 10 | 14 + 20 | 21 + 30 | 22 |
| 105386 | BT-HP.32-SST-p-M8x40 | 32 | 23 | M8 | 17 | 6.5     | 8.5 | 40 | 10 | 4  | 9 | 7 + 10 | 14 + 20 | 21 + 30 | 27 |