



















- 1 
- 2 
- 3 
- 4 
- 5 
- 6 
- 7 
- 8 
- 9 
- 10 
- 11 
- 12 
- 13 
- 14 
- 15 
- 16 
- 17 
- 18 

MATERIAL

Stator, rotor, closing lever and nut (M22x1.5) in glass-fibre reinforced polyamide based (PA) technopolymer certified self-extinguish UL-94 V0, black colour, matte finish.

PACKING RING

SBR rubber.

INTERNAL TOOTHED WASHER

AISI 304 stainless steel

SELF-TAPPING SCREW

AISI 304 stainless steel

KEY

Polyamide based (PA) technopolymer.

ROTATION

90°.

IP PROTECTION

IP 65 protection class according to EN 60529 (see page A-18).

STANDARD EXECUTIONS

- **CQT/A**: mark for two-wings key.
- **CQT/T**: mark for triangular key.

TECHNICAL DATA



The "V0" certification in accordance with UL-94 V (Underwriters Laboratories) (see Technical data on page A-5) indicates that on a plastic test sample with specific shape and dimensions, in the vertical position, the flame is extinguished within 10 seconds, without generating incandescent drops.

SPECIAL EXECUTIONS ON REQUEST

- Cylindrical body of the closing lever in other dimensions.
- Latches and keys supplied separately.



Drilling template



CQT/A

Code	Description	D	H	l	l1	l2	h	ΔΔ
421393	CQT/A-32-18 AE-V0	28	32	20	20	18	4	20
421391	CQT/A-32-20 AE-V0	28	32	20	20	20	4	20
421395	CQT/A-32-24 AE-V0	28	32	20	20	24	4	21
421397	CQT/A-32-32 AE-V0	28	32	20	20	32	4	23

CQT/T

Code	Description	D	H	l	l1	l2	h	ΔΔ
421403	CQT/T-32-18 AE-V0	28	32	20	20	18	4	20
421401	CQT/T-32-20 AE-V0	28	32	20	20	20	4	20
421405	CQT/T-32-24 AE-V0	28	32	20	20	24	4	21
421407	CQT/T-32-32 AE-V0	28	32	20	20	32	4	23