

STANDARD EXECUTIONS

- **DVA.1**: threaded studs and base plate in polished zinc-plated steel, vibration-damper body in natural rubber NR, black colour, hardness 40, 55, 70 Shore A ± 5 .
- **DVA.1-SST**: threaded studs and base plate in INOX AISI 304 stainless steel, vibration-damper body in natural rubber NR, black colour, hardness 55 Shore A ± 5 .

FEATURES AND APPLICATIONS


The rubber buffers have been designed to damp vibrations, shocks and noises produced by moving bodies or non-balanced vibrating masses of equipment and machines which can cause:

- malfunctioning and reduction of the machine lifespan and/or of the adjacent ones;
- damage to health;
- noise.

Load diagrams for each single code are available on request.
See Technical data and guidelines for the choice (on page 728).

SPECIAL EXECUTIONS ON REQUEST

Natural rubber NR, hardness 40, 70 tolerance ± 5 Shore A for executions with AISI 304 stainless steel base.




* Complete the description with the desired hardness:
40, 55 or 70 tolerance ± 5 Shore A.

DVA.1 - 8 - 8 - M3 - 6 - 55
D L d I Shore A

DVA.1

Description						Hardness 40 Shore A				Hardness 55 Shore A				Hardness 70 Shore A			
						Code	Max load [N]	Max deflection [mm]	Stiffness [N/mm]	Code	Max load [N]	Max deflection [mm]	Stiffness [N/mm]	Code	Max load [N]	Max deflection [mm]	Stiffness [N/mm]
DVA.1-6-7-M3-6-*	6	7	M3	3	1	413781	33	2	19	410901	42	2	24	416491	90	2	51
DVA.1-8-8-M3-6-*	8	8	M3	6	1	413801	50	2	25	411101	85	2	43	416501	150	2	75
DVA.1-8-13-M3-6-*	8	13	M3	6	2	413803	62	3	19	411003	94	3	29	416503	133	3	41
DVA.1-10-10-M4-10-*	10	10	M4	10	2	413811	75	3	30	411121	100	3	40	416511	200	3	80
DVA.1-10-15-M4-10-*	10	15	M4	10	3	413821	65	4	17	411131	100	4	26	416521	150	4	40
DVA.1-10-20-M4-10-*	10	20	M4	10	3	413823	59	5	12	411133	93	5	19	416523	96	5	19
DVA.1-15-8-M4-10-*	15	8	M4	10	5	413831	437	2	219	411141	537	2	269	416531	1325	2	663
DVA.1-15-10-M4-10-*	15	10	M4	10	6	413841	210	3	84	411151	325	3	130	416541	717	3	287
DVA.1-15-15-M4-10-*	15	15	M4	10	7	413851	155	4	41	411161	280	4	75	416551	513	4	137
DVA.1-15-20-M4-10-*	15	20	M4	10	8	413861	151	5	30	411171	234	5	47	416561	468	5	94
DVA.1-15-25-M4-10-*	15	25	M4	10	9	413863	133	6	21	411019	234	6	37	411173	498	6	80
DVA.1-20-8,5-M6-18-*	20	8.5	M6	6	13	413869	1410	2	671	411176	2092	2	996	416569	6150	2	2928
DVA.1-20-15-M6-18-*	20	15	M6	18	18	413871	322	4	86	411181	479	4	128	416571	1044	4	278
DVA.1-20-20-M6-18-*	20	20	M6	18	25	413881	220	5	44	411201	430	5	86	416581	995	5	199
DVA.1-20-25-M6-18-*	20	25	M6	18	20	413891	264	6	42	411211	433	6	69	416591	1010	6	162
DVA.1-20-30-M6-18-*	20	30	M6	18	23	413893	214	8	29	411213	417	8	56	416593	978	8	130
DVA.1-25-10-M6-18-*	25	10	M6	18	25	413899	4000	2	1600	411216	5990	2	2396	416599	10020	2	4008
DVA.1-25-15-M6-18-*	25	15	M6	18	28	413901	860	4	229	411221	1068	4	285	416601	2690	4	717
DVA.1-25-20-M6-18-*	25	20	M6	18	31	413911	391	5	78	411241	620	5	124	416611	1533	5	307
DVA.1-25-25-M6-18-*	25	25	M6	18	35	413921	441	6	71	411261	529	6	85	416621	1374	6	220
DVA.1-25-30-M6-18-*	25	30	M6	18	38	413931	432	8	58	411271	524	8	70	416631	1208	8	161

DVA.1



* Complete the description with the desired hardness:
40, 55 or 70 tolerance ± 5 Shore A.


DVA.1 - 8 - 8 - M3 - 6 - 55
D L d I Shore A

DVA.1						Hardness 40 Shore A				Hardness 55 Shore A				Hardness 70 Shore A			
Description	D	L	d	I		Code	Max load [N]	Max deflection [mm]	Stiffness [N/mm]	Code	Max load [N]	Max deflection [mm]	Stiffness [N/mm]	Code	Max load [N]	Max deflection [mm]	Stiffness [N/mm]
DVA.1-30-15-M8-20-*	30	15	M8	20	45	413941	986	4	263	411281	2100	1.5	1400	416641	2700	1.5	1800
DVA.1-30-15-M8-25-*	30	15	M8	25	46	413942	986	4	262	411282	2080	3.75	554	416642	3300	4	880
DVA.1-30-20-M8-20-*	30	20	M8	20	50	413951	770	5	154	411301	1067	5	213	416651	2260	5	452
DVA.1-30-25-M8-20-*	30	25	M8	20	54	413956	651	6	104	411311	1095	6	175	416656	1560	6	250
DVA.1-30-30-M8-20-*	30	30	M8	20	57	413961	500	8	67	411321	1055	8	141	416661	1960	8	261
DVA.1-30-30-M8-25-*	30	30	M8	25	58	413962	500	8	66	411322	1055	7.5	140	416662	1960	8	261
DVA.1-30-40-M8-20-*	30	40	M8	20	65	413963	649	10	65	411323	932	10	93	416663	2000	10	200
DVA.1-30-40-M8-25-*	30	40	M8	25	65	413964	649	10	64	411324	932	10	93	416664	2000	10	200
DVA.1-40-20-M8-23-*	40	20	M8	23	80	413971	1800	5	360	411331	2430	5	486	416671	4450	5	890
DVA.1-40-20-M10-23-*	40	20	M10	23	79	413994	1628	5	326	411333	3160	5	632	416693	5550	5	1110
DVA.1-40-25-M10-23-*	40	25	M10	23	88	413995	1380	6	221	411336	2280	6.2	365	416695	4150	6	664
DVA.1-40-30-M8-23-*	40	30	M8	23	95	413981	1137	8	152	411341	1574	8	210	416681	3420	8	456
DVA.1-40-40-M8-23-*	40	40	M8	23	100	413991	1056	10	106	411361	1397	10	140	416691	3190	10	319
DVA.1-40-45-M10-23-*	40	45	M8	23	105	413997	1040	11	92	411351	1825	11.3	92	416697	2870	11	92.4
DVA.1-50-20-M10-28-*	50	20	M10	28	130	414001	3030	5	606	411381	4100	5	820	416701	9240	5	1848
DVA.1-50-25-M10-28-*	50	25	M10	28	150	414006	2355	6	377	411386	3640	6.3	582	416706	7550	6	1208
DVA.1-50-30-M10-28-*	50	30	M10	28	184	414011	2010	8	268	411401	3300	8	440	416711	5450	8	727
DVA.1-50-35-M10-28-*	50	35	M10	28	167	414016	1965	9	1965	411411	3050	9	3050	416716	5750	9	5750
DVA.1-50-40-M10-28-*	50	40	M10	28	170	414021	1477	10	148	411421	2130	10	213	416721	4940	10	494
DVA.1-50-45-M10-28-*	50	45	M10	28	180	414031	1368	11	122	411441	2046	11	182	416731	2580	11	229
DVA.1-50-50-M10-28-*	50	50	M10	28	195	414041	1500	13	120	411446	2188	13	175	416741	4750	13	380
DVA.1-60-30-M10-28-*	60	30	M10	28	211	414051	3020	8	403	411451	4170	8	556	416751	9130	8	1217
DVA.1-60-40-M10-28-*	60	40	M10	28	236	414061	2520	10	252	411456	3610	10	361	416761	6950	10	695
DVA.1-60-50-M10-28-*	60	50	M10	28	261	414063	2458	13	197	411457	3410	13	273	416763	6570	13	526
DVA.1-70-30-M10-28-*	70	30	M10	28	297	414070	6370	8	849	411460	8570	8	1143	416770	24010	8	3382
DVA.1-70-35-M10-28-*	70	35	M10	28	320	414072	5200	9	5200	411463	8660	9	8660	416769	14480	9	14480
DVA.1-70-45-M10-28-*	70	45	M10	28	380	414071	3810	11	339	411461	7130	11	634	416771	13210	11	1174
DVA.1-75-25-M12-37-*	75	25	M12	37	345	414081	11000	6	1760	411471	12970	6	2075	416781	25000	6	4000
DVA.1-75-40-M12-37-*	75	40	M12	37	410	414091	4910	10	491	411481	6970	10	697	416791	15380	10	1538
DVA.1-75-50-M12-37-*	75	50	M12	37	500	414096	4470	12	358	411486	6950	12	556	416786	12800	12	1024
DVA.1-75-55-M12-37-*	75	55	M12	37	515	414101	3470	14	252	411501	7510	14	546	416801	11240	14	817
DVA.1-80-30-M14-37-*	80	30	M14	37	600	414105	9690	5	1938	411511	15510	5	3102	416805	22930	4	5097
DVA.1-80-40-M14-37-*	80	40	M14	37	650	414106	7300	10	730	411516	10510	10	1051	416807	19690	10	1969
DVA.1-100-40-M16-41-*	100	40	M16	41	765	414111	13990	10	1399	411521	20000	10	2000	416811	29000	10	2900
DVA.1-100-55-M16-41-*	100	55	M16	41	905	414121	7320	14	532	411541	13080	14	951	416821	24260	14	1764
DVA.1-100-60-M16-41-*	100	60	M16	41	950	414131	7000	15	467	411561	11290	15	753	416831	28500	15	1900
DVA.1-100-75-M16-41-*	100	75	M16	41	1090	414141	7790	19	415	411581	9640	19	514	416841	22350	19	1192
DVA.1-125-55-M16-41-*	125	55	M16	41	1320	414161	17270	14	1256	411601	19260	14	1401	416901	23610	8	3008
DVA.1-125-75-M16-41-*	125	75	M16	41	1625	414163	12235	19	653	411603	19440	19	1037	416903	21789	19	1162



Vibration damping elements

IVA.1-SST



DVA.1 - 8 - 8 - SST - M3 - 6 - 55

D L d l Shore A

Description	D	L	d	l	Shore A	Hardness 40 Shore A			Hardness 55 Shore A			Hardness 70 Shore A		
						Code	Max load [N]	Max deflection [mm]	Stiffness [N/mm]	Code	Max load. [N]	Max deflection [mm]	Stiffness [N/mm]	Code
DVA.1-6-7-SST-M3-6-55	6	7	M3	6	1		33	2	19	409901	42	2	24	
DVA.1-8-8-SST-M3-6-55	8	8	M3	6	1		50	2	25	410001	85	2	43	
DVA.1-8-13-SST-M3-6-55	8	13	M3	6	2		62	3	19	410003	94	3	29	
DVA.1-10-10-SST-M4-10-55	10	10	M4	10	2		75	3	30	410005	100	3	40	
DVA.1-10-15-SST-M4-10-55	10	15	M4	10	3		65	4	17	410007	100	4	26	
DVA.1-10-20-SST-M4-10-55	10	20	M4	10	3		59	5	12	410009	93	5	19	
DVA.1-15-8-SST-M4-10-55	15	8	M4	10	5		437	2	219	410011	537	2	269	
DVA.1-15-10-SST-M4-10-55	15	10	M4	10	6		210	3	84	410013	325	3	130	
DVA.1-15-15-SST-M4-10-55	15	15	M4	10	7		155	4	41	410015	280	4	75	
DVA.1-15-20-SST-M4-10-55	15	20	M4	10	8		151	5	30	410017	234	5	47	
DVA.1-15-25-SST-M4-10-55	15	25	M4	10	9		133	6	21	410019	234	6	37	
DVA.1-20-8-5-SST-M6-18-55	20	8.5	M6	18	13		1410	2	671	410020	2092	2	996	
DVA.1-20-15-SST-M6-18-55	20	15	M6	18	18		322	4	86	410021	479	4	128	
DVA.1-20-20-SST-M6-18-55	20	20	M6	18	25		220	5	44	410023	430	5	86	
DVA.1-20-25-SST-M6-18-55	20	25	M6	18	20		264	6	42	410025	433	6	69	
DVA.1-20-30-SST-M6-18-55	20	30	M6	18	23		214	8	29	410027	417	8	56	
DVA.1-25-10-SST-M6-18-55	25	10	M6	18	25		4000	2	1600	410030	5990	2.5	2396	
DVA.1-25-15-SST-M6-18-55	25	15	M6	18	28		860	4	229	410031	1068	4	285	
DVA.1-25-20-SST-M6-18-55	25	20	M6	18	31		391	5	78	410033	620	5	124	
DVA.1-25-25-SST-M6-18-55	25	25	M6	18	35		441	6	71	410035	529	6	85	
DVA.1-25-30-SST-M6-18-55	25	30	M6	18	38		432	8	58	410037	524	8	70	
DVA.1-30-15-SST-M8-20-55	30	15	M8	20	45		986	4	263	410041	2080	4	555	
DVA.1-30-15-SST-M8-25-55	30	15	M8	25	46		986	4	262	410042	2080	4	554	
DVA.1-30-20-SST-M8-20-55	30	20	M8	20	50		770	5	154	410043	1067	5	213	
DVA.1-30-25-SST-M8-20-55	30	25	M8	20	54		651	6	104	410044	1095	6	175	
DVA.1-30-30-SST-M8-20-55	30	30	M8	20	57		500	8	67	410045	1055	8	141	
DVA.1-30-30-SST-M8-25-55	30	30	M8	25	58		500	8	67	410046	1055	8	140	
DVA.1-30-40-SST-M8-20-55	30	40	M8	20	65		649	10	65	410047	932	10	93	
DVA.1-30-40-SST-M8-25-55	30	40	M8	25	65		649	10	65	410048	932	10	93	
DVA.1-40-20-SST-M8-23-55	40	20	M8	23	80		1800	5	360	410051	2430	5	486	
DVA.1-40-20-SST-M10-23-55	40	20	M10	23	79		1628	5	326	410050	3160	5	632	
DVA.1-40-25-SST-M10-23-55	40	20	M10	23	88		1380	6	221	410052	2280	6.2	365	
DVA.1-40-30-SST-M8-23-55	40	30	M8	23	95		1137	8	152	410053	1574	8	210	
DVA.1-40-40-SST-M8-23-55	40	40	M8	23	100		1056	10	106	410055	1397	10	140	
DVA.1-40-45-SST-M10-23-55	40	45	M10	23	105		1040	11	92	410057	1825	11.3	162	
DVA.1-50-20-SST-M10-28-55	50	20	M10	28	130		3030	5	606	410061	4100	5	820	
DVA.1-50-25-SST-M10-28-55	50	24	M10	28	150		2355	6	377	410062	3640	6.2	582	
DVA.1-50-30-SST-M10-28-55	50	30	M10	28	184		2010	8	268	410063	3300	8	440	
DVA.1-50-35-SST-M10-28-55	50	35	M10	28	167		1965	9	1965	410064	3050	8.7	348.5	
DVA.1-50-40-SST-M10-28-55	50	40	M10	28	170		1477	10	148	410065	2130	10	213	
DVA.1-50-45-SST-M10-28-55	50	45	M10	28	180		1368	11	122	410067	2046	11	182	
DVA.1-50-50-SST-M10-28-55	50	50	M10	28	195		1500	13	120	410069	2188	13	175	
DVA.1-60-30-SST-M10-28-55	60	30	M10	28	211		3020	8	403	410071	4170	8	556	
DVA.1-60-40-SST-M10-28-55	60	40	M10	28	236		2520	10	252	410073	3610	10	361	
DVA.1-60-50-SST-M10-28-55	60	50	M10	28	261		2458	13	197	410075	3410	13	273	
DVA.1-70-30-SST-M10-28-55	70	30	M10	28	297		6370	8	849	410076	8570	8	1143	
DVA.1-70-35-SST-M10-28-55	70	35	M10	28	320		5200	9	5200	410078	8570	9	990	
DVA.1-70-45-SST-M10-28-55	70	45	M10	28	380		3810	11	339	410077	7130	11	634	
DVA.1-75-25-SST-M12-37-55	75	25	M12	37	345		11000	6	1760	410081	12970	6	2075	
DVA.1-75-40-SST-M12-37-55	75	40	M12	37	410		4910	10	491	410083	6970	10	697	
DVA.1-75-50-SST-M12-37-55	75	50	M12	37	500		4470	12	358	410084	6950	12	556	
DVA.1-75-55-SST-M12-37-55	75	55	M12	37	515		3470	14	252	410085	7510	14	546	
DVA.1-80-30-SST-M14-37-55	80	30	M14	37	600		9690	5	1938	410087	15510	5	3102	
DVA.1-80-40-SST-M14-37-55	80	40	M14	37	650		7300	10	730	410088	10510	10	1051	
DVA.1-100-40-SST-M16-41-55	100	40	M16	41	765		13990	10	1399	410091	20000	10	2000	
DVA.1-100-55-SST-M16-41-55	100	55	M16	41	905		7320	14	532	410093	13080	14	951	
DVA.1-100-60-SST-M16-41-55	100	60	M16	41	950		7000	15	467	410095	11290	15	753	
DVA.1-100-75-SST-M16-41-55	100	75	M16	41	1090		7790	19	415	410097	9640	19	514	
DVA.1-125-55-SST-M16-41-55	125	55	M16	41	1320		17270	14	1256	410098	19260	14	1401	
DVA.1-125-75-SST-M16-41-55	125	75	M16	41	1600		12235	19	653	410099	19440	19	1037	