

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

STANDARD EXECUTION

Bushing with threaded blind hole and base plate in AISI 304 stainless steel.

VIBRATION-DAMPER BODY

Silicone rubber (MVQ) RAL 7040 (C33) grey or RAL 5002 (C52) blue colour, in compliance with FDA (U.S. Food and Drug Administration), giving the possibility to use in the food and medical industry.

- Hardness 55 Shore A \pm 5.
- High resistance to ageing.
- Resistance to high temperatures (up to 200°C) and low temperatures (-50°C).

FEATURES AND APPLICATIONS


The rubber buffers have been designed to damp vibrations, shocks and noises produced by moving bodies or non-balanced vibrating masses of equipment and machines. DVF.7 elements are generally used as a bumper or as a limit stop for the absorption of vibrations, and for preventing:

- malfunctioning and reduction of the machine lifespan and/or of the adjacent ones;
- noise and thus also damage to health.

Load diagrams for each single code are available on request. See Technical data and guidelines for the choice (on page).

SPECIAL EXECUTIONS ON REQUEST

Silicone rubber (MVQ) in compliance with FDA, hardness 40, 70 Shore A \pm 5.



DVF.7 - 20 - 17 - SST - M5 - 55
 D L Stainless steel d Shore A

C33 RAL7040 C52 RAL5002

Code	Description	D	L	d	d1	h	Max load [N]	Max. deflection [mm]	Stiffness [N/mm]	⚖️
432901	DVF.7-20-17-SST-M5-55-C33	20	17	M5	10	5	211	4.25	50	16
432902	DVF.7-20-17-SST-M6-55-C33	20	17	M6	10	6	211	4.25	50	14
432906	DVF.7-25-17-SST-M6-55-C33	25	17	M6	19	6	605	4.25	142	15
432951	DVF.7-25-20-SST-M6-55-C33	25	20	M6	16	7	420	5	84	14
432911	DVF.7-32-22-SST-M8-55-C33	32	22	M8	24	8	778	5.5	142	18
432953	DVF.7-32-26-SST-M8-55-C33	32	26	M8	21	9	550	6.5	84	23
432955	DVF.7-38-32-SST-M8-55-C33	38	32	M8	24	10	861	8	107	23
432956	DVF.7-38-32-SST-M10-55-C33	38	32	M10	24	10	861	8	107	23
432916	DVF.7-38-35-SST-M8-55-C33	38	35	M8	30	8	1455	8.75	166	23
432917	DVF.7-38-35-SST-M10-55-C33	38	35	M10	30	10	1455	8.75	166	70
432921	DVF.7-43-50-SST-M10-55-C33	43	50	M10	30	10	1420	12.5	114	98
432931	DVF.7-50-20-SST-M10-55-C33	50	20	M10	40	10	3010	5	602	75
432959	DVF.7-50-43-SST-M10-55-C33	50	43	M10	32	11	1396	10.75	130	88
432941	DVF.7-60-40-SST-M10-55-C33	60	40	M10	40	10	2990	10	299	125
432903	DVF.7-20-17-SST-M5-55-C52	20	17	M5	10	5	211	4.25	50	16
432904	DVF.7-20-17-SST-M6-55-C52	20	17	M6	10	6	211	4.25	50	14
432908	DVF.7-25-17-SST-M6-55-C52	25	17	M6	19	6	605	4.25	142	15
432952	DVF.7-25-20-SST-M6-55-C52	25	20	M6	16	7	420	5	84	14
432913	DVF.7-32-22-SST-M8-55-C52	32	22	M8	24	8	778	5.5	142	18
432954	DVF.7-32-26-SST-M8-55-C52	32	26	M8	21	9	550	6.5	84	25
432957	DVF.7-38-32-SST-M8-55-C52	38	32	M8	24	10	861	8	107	42
432958	DVF.7-38-32-SST-M10-55-C52	38	32	M10	24	10	861	8	107	42
432918	DVF.7-38-35-SST-M8-55-C52	38	35	M8	30	8	1455	8.75	166	74
432919	DVF.7-38-35-SST-M10-55-C52	38	35	M10	30	10	1455	8.75	166	70
432926	DVF.7-43-50-SST-M10-55-C52	43	50	M10	30	10	1420	12.5	114	98
432936	DVF.7-50-20-SST-M10-55-C52	50	20	M10	40	10	3010	5	602	75
432960	DVF.7-50-43-SST-M10-55-C52	50	43	M10	32	11	1396	10.75	130	83
432946	DVF.7-60-40-SST-M10-55-C52	60	40	M10	40	10	2990	10	299	125

Vibration damping elements