



**MATERIAL**

Matte anodised aluminium.

**MOUNTING**


By means of three supplied self-tapping rivets for fitting to control knobs IZN.381 (see page 422).

**STANDARD EXECUTIONS**

- **F.N**: plain flange.
- **F.K**: flange with triangular black index.
- **F.GS**: flange with black graduation (marks and numbers).
- **F.32 GS e F.40 GS**: 40 marks, numbering 0, 1, 2 .... 9 increases as the knob is turned clockwise.
- **F.45, 50, 63 GS**: 100 marks, numbering 0, 1, 2 .... 9 increases as the knob is turned clockwise.

**SPECIAL EXECUTIONS ON REQUEST**

On the surface of the flanges other kinds of precision graduations can be laser-engraved (see Graduations on page 439), numbers, graphic symbols, etc.



**F.N**

| Code  | Description | D  | F  | d   | d1 | h3 | s   | r    | ⚖  |
|-------|-------------|----|----|-----|----|----|-----|------|----|
| 29002 | F.32 N      | 32 | 38 | 2.1 | 15 | 6  | 0.8 | 9.5  | 3  |
| 30102 | F.40 N      | 42 | 50 | 3   | 18 | 7  | 1   | 14   | 7  |
| 30202 | F.45 N      | 48 | 55 | 2.7 | 22 | 7  | 1   | 15.8 | 8  |
| 30302 | F.50 N      | 52 | 63 | 2.7 | 22 | 9  | 1   | 18.1 | 10 |
| 30452 | F.63 N      | 63 | 78 | 2.7 | 26 | 13 | 1   | 22.7 | 16 |

**F.K**

| Code  | Description | D  | F  | d   | d1 | h3 | s   | r    | ⚖  |
|-------|-------------|----|----|-----|----|----|-----|------|----|
| 29004 | F.32 K      | 32 | 38 | 2.1 | 15 | 6  | 0.8 | 9.5  | 3  |
| 30104 | F.40 K      | 42 | 50 | 3   | 18 | 7  | 1   | 14   | 7  |
| 30204 | F.45 K      | 48 | 55 | 2.7 | 22 | 7  | 1   | 15.8 | 8  |
| 30304 | F.50 K      | 52 | 63 | 2.7 | 22 | 9  | 1   | 18.1 | 10 |
| 30454 | F.63 K      | 63 | 78 | 2.7 | 26 | 13 | 1   | 22.7 | 16 |

**F.GS**

| Code  | Description    | D  | F  | d   | d1 | h3 | s   | r    | ⚖  |
|-------|----------------|----|----|-----|----|----|-----|------|----|
| 29003 | F.32 GS-10/40  | 32 | 38 | 2.1 | 15 | 6  | 0.8 | 9.5  | 3  |
| 30103 | F.40 GS-10/40  | 42 | 50 | 3   | 18 | 7  | 1   | 14   | 7  |
| 30203 | F.45 GS-10/100 | 48 | 55 | 2.7 | 22 | 7  | 1   | 15.8 | 8  |
| 30303 | F.50 GS-10/100 | 52 | 63 | 2.7 | 22 | 9  | 1   | 18.1 | 10 |
| 30453 | F.63 GS-10/100 | 63 | 78 | 2.7 | 26 | 13 | 1   | 22.7 | 16 |