

MATERIAL

Cast AISI CF-8 stainless steel, sandblasted matte finish.

AISI 304 stainless steel screws and nuts.



Polyamide based (PA) or polytetrafluoroethylene based (PTFE) technopolymer sliding bushing (d1).

FEATURES AND APPLICATIONS

GN 131.1-NI connecting clamps can normally be matched with the linear actuators.

By clamping the guide hole d1 it is possible to adjust the actuator positioning and to lock the slider after having set up the final position.

The clamping screws d3 may be replaced by clamping kits GN 911 – GN 911.3 (see page 1372).



Code	Description	d1##	d2#	d3	d4	k	l	m	d3 Clamping kit	⚖
GN.42213	GN 131.1-G18-B18-2-NI	18	18	M6	M3	25	64	20	GN 911-M6-22	142

Hole without sliding bushing.

Hole with sliding bushing.