

## MATERIAL

Cast AISI CF-8 stainless steel, sandblasted matte finish.

AISI 304 stainless steel screws and nuts.



Polyamide based (PA) or polytetrafluoroethylene based (PTFE) technopolymer sliding bushings.

## FEATURES AND APPLICATIONS

GN 131.2-NI connecting clamps can normally be matched with the linear actuators.

By clamping the guide holes d1/d2 it is possible to adjust the actuator positioning and to lock the slider after having set up the final position.

The clamping screws d3 may be replaced by clamping kits GN 911 – GN 911.3 (see page 1372).



Code	Description	d1##	d2##	d3	d4	k	l	m	d3 Clamping kit	⚖
GN.42313	GN 131.2-G18-G18-2-NI	18	18	M6	M3	25	64	20	GN 911-M6-22	148

## Hole with sliding bushing.