



BASE

AISI 316L stainless steel, turned finish.

THREADED STEM

AISI 316L stainless steel

STANDARD EXECUTIONS

- **GN 22-D0-SK**: without no-slip disk, with adjusting hexagon
- **GN 22-D0-TK**: without no-slip disk, with milled flat faces at the base
- **GN 22-D1-SK**: with no-slip disk, with adjusting hexagon
- **GN 22-D1-TK**: with no-slip disk, with milled flat faces at the base

HEX NUT ISO 4032

Stainless steel

MOUNTING SCREW

Stainless steel

NO-SLIP DISK

Acrylonitrile butadiene rubber (NBR)

- Black colour
- Hardness 70 Shore A
- Mounted


FEATURES

GN 22 levelling feet are particularly suitable for use in aggressive environments.

They are supplied assembled and cannot be disassembled.



GN 22-D0-SK



GN 22-D0-SK


Code	Description	d1	d2	h1	h3	l1	sw1	Static load [kN]	⚖️
GN.80651	GN 22-80-M8-40-D0-SK	80	M 8	8.5	19.5	40	17	6	275
GN.80653	GN 22-80-M8-50-D0-SK	80	M 8	8.5	19.5	50	17	6	279
GN.80655	GN 22-80-M8-63-D0-SK	80	M 8	8.5	19.5	63	17	6	284
GN.80661	GN 22-80-M10-50-D0-SK	80	M 10	8.5	19.5	50	17	11	295
GN.80663	GN 22-80-M10-60-D0-SK	80	M 10	8.5	19.5	60	17	11	301
GN.80665	GN 22-80-M10-80-D0-SK	80	M 10	8.5	19.5	80	17	11	313
GN.80667	GN 22-80-M10-100-D0-SK	80	M 10	8.5	19.5	100	17	11	326
GN.80671	GN 22-80-M12-60-D0-SK	80	M 12	8.5	19.5	60	17	16	323
GN.80673	GN 22-80-M12-80-D0-SK	80	M 12	8.5	19.5	80	17	16	341
GN.80675	GN 22-80-M12-100-D0-SK	80	M 12	8.5	19.5	100	17	16	358
GN.80677	GN 22-80-M12-125-D0-SK	80	M 12	8.5	19.5	125	17	16	380
GN.80801	GN 22-100-M8-40-D0-SK	100	M 8	9	20.5	40	17	6	453
GN.80803	GN 22-100-M8-50-D0-SK	100	M 8	9	20.5	50	17	6	457
GN.80805	GN 22-100-M8-63-D0-SK	100	M 8	9	20.5	63	17	6	462
GN.80741	GN 22-100-M10-50-D0-SK	100	M 10	9	20.5	50	17	11	473
GN.80743	GN 22-100-M10-60-D0-SK	100	M 10	9	20.5	60	17	11	479
GN.80745	GN 22-100-M10-80-D0-SK	100	M 10	9	20.5	80	17	11	491
GN.80747	GN 22-100-M10-100-D0-SK	100	M 10	9	20.5	100	17	11	504
GN.80751	GN 22-100-M12-60-D0-SK	100	M 12	9	20.5	60	17	16	501
GN.80753	GN 22-100-M12-80-D0-SK	100	M 12	9	20.5	80	17	16	518
GN.80755	GN 22-100-M12-100-D0-SK	100	M 12	9	20.5	100	17	16	536
GN.80757	GN 22-100-M12-125-D0-SK	100	M 12	9	20.5	125	17	16	558

INOX
STAINLESS
STEEL



Levelling feet and supports


GN 22-D1-SK




GN 22-D1-SK

INOX STAINLESS STEEL

Code	Description	d1	d2	h1	h2	h3	l1	sw1	Static load [KN]	
GN.80652	GN 22-80-M8-40-D1-SK	80	M 8	8.5	2	19.5	40	17	6	295
GN.80654	GN 22-80-M8-50-D1-SK	80	M 8	8.5	2	19.5	50	17	6	299
GN.80656	GN 22-80-M8-63-D1-SK	80	M 8	8.5	2	19.5	63	17	6	304
GN.80662	GN 22-80-M10-50-D1-SK	80	M 10	8.5	2	19.5	50	17	11	316
GN.80664	GN 22-80-M10-60-D1-SK	80	M 10	8.5	2	19.5	60	17	11	322
GN.80666	GN 22-80-M10-80-D1-SK	80	M 10	8.5	2	19.5	80	17	11	334
GN.80668	GN 22-80-M10-100-D1-SK	80	M 10	8.5	2	19.5	100	17	11	346
GN.80672	GN 22-80-M12-60-D1-SK	80	M 12	8.5	2	19.5	60	17	16	343
GN.80674	GN 22-80-M12-80-D1-SK	80	M 12	8.5	2	19.5	80	17	16	361
GN.80676	GN 22-80-M12-100-D1-SK	80	M 12	8.5	2	19.5	100	17	16	379
GN.80678	GN 22-80-M12-125-D1-SK	80	M 12	8.5	2	19.5	125	17	16	401
GN.80802	GN 22-100-M8-40-D1-SK	100	M 8	9	3	20.5	40	17	6	495
GN.80804	GN 22-100-M8-50-D1-SK	100	M 8	9	3	20.5	50	17	6	499
GN.80806	GN 22-100-M8-63-D1-SK	100	M 8	9	3	20.5	63	17	6	504
GN.80742	GN 22-100-M10-50-D1-SK	100	M 10	9	3	20.5	50	17	11	515
GN.80744	GN 22-100-M10-60-D1-SK	100	M 10	9	3	20.5	60	17	11	521
GN.80746	GN 22-100-M10-80-D1-SK	100	M 10	9	3	20.5	80	17	11	534
GN.80748	GN 22-100-M10-100-D1-SK	100	M 10	9	3	20.5	100	17	11	546
GN.80752	GN 22-100-M12-60-D1-SK	100	M 12	9	3	20.5	60	17	16	543
GN.80754	GN 22-100-M12-80-D1-SK	100	M 12	9	3	20.5	80	17	16	561
GN.80756	GN 22-100-M12-100-D1-SK	100	M 12	9	3	20.5	100	17	16	578
GN.80758	GN 22-100-M12-125-D1-SK	100	M 12	9	3	20.5	125	17	16	601



GN 22-D0-TK




INOX STAINLESS STEEL

GN 22-D0-TK

Code	Description	d1	d2	h1	h4	l1	sw2	Static load [KN]	⚖
GN.80681	GN 22-80-M16-75-D0-TK	80	M 16	8.5	25.5	75	12	17	416
GN.80683	GN 22-80-M16-100-D0-TK	80	M 16	8.5	25.5	100	12	17	455
GN.80685	GN 22-80-M16-125-D0-TK	80	M 16	8.5	25.5	125	12	17	494
GN.80687	GN 22-80-M16-150-D0-TK	80	M 16	8.5	25.5	150	12	17	534
GN.80689	GN 22-80-M16-200-D0-TK	80	M 16	8.5	25.5	200	12	17	612
GN.80691	GN 22-80-M16-250-D0-TK	80	M 16	8.5	25.5	250	12	17	690
GN.80701	GN 22-80-M20-75-D0-TK	80	M 20	8.5	27	75	15	28	529
GN.80703	GN 22-80-M20-100-D0-TK	80	M 20	8.5	27	100	15	28	590
GN.80705	GN 22-80-M20-125-D0-TK	80	M 20	8.5	27	125	15	28	651
GN.80707	GN 22-80-M20-150-D0-TK	80	M 20	8.5	27	150	15	28	713
GN.80709	GN 22-80-M20-200-D0-TK	80	M 20	8.5	27	200	15	28	835
GN.80711	GN 22-80-M20-250-D0-TK	80	M 20	8.5	27	250	15	28	958
GN.80721	GN 22-80-M24-100-D0-TK	80	M 24	8.5	30.5	100	19	46	775
GN.80723	GN 22-80-M24-125-D0-TK	80	M 24	8.5	30.5	125	19	46	863
GN.80725	GN 22-80-M24-150-D0-TK	80	M 24	8.5	30.5	150	19	46	951
GN.80727	GN 22-80-M24-200-D0-TK	80	M 24	8.5	30.5	200	19	46	1130
GN.80729	GN 22-80-M24-300-D0-TK	80	M 24	8.5	30.5	300	19	46	1480
GN.80761	GN 22-100-M16-75-D0-TK	100	M 16	9	26.5	75	12	17	594
GN.80763	GN 22-100-M16-100-D0-TK	100	M 16	9	26.5	100	12	17	633
GN.80765	GN 22-100-M16-125-D0-TK	100	M 16	9	26.5	125	12	17	673
GN.80767	GN 22-100-M16-150-D0-TK	100	M 16	9	26.5	150	12	17	712
GN.80769	GN 22-100-M16-200-D0-TK	100	M 16	9	26.5	200	12	17	790
GN.80771	GN 22-100-M16-250-D0-TK	100	M 16	9	26.5	250	12	17	869
GN.80781	GN 22-100-M20-75-D0-TK	100	M 20	9	28	75	15	28	706
GN.80783	GN 22-100-M20-100-D0-TK	100	M 20	9	28	100	15	28	767
GN.80785	GN 22-100-M20-125-D0-TK	100	M 20	9	28	125	15	28	828
GN.80787	GN 22-100-M20-150-D0-TK	100	M 20	9	28	150	15	28	889
GN.80789	GN 22-100-M20-200-D0-TK	100	M 20	9	28	200	15	28	1010
GN.80791	GN 22-100-M20-250-D0-TK	100	M 20	9	28	250	15	28	1135
GN.80807	GN 22-100-M24-100-D0-TK	100	M 24	9	31.5	100	19	46	953
GN.80809	GN 22-100-M24-125-D0-TK	100	M 24	9	31.5	125	19	46	1040
GN.80811	GN 22-100-M24-150-D0-TK	100	M 24	9	31.5	150	19	46	1130
GN.80813	GN 22-100-M24-200-D0-TK	100	M 24	9	31.5	200	19	46	1305
GN.80815	GN 22-100-M24-300-D0-TK	100	M 24	9	31.5	300	19	46	1660
GN.80821	GN 22-120-M20-75-D0-TK	120	M 20	12	32	75	15	28	1080
GN.80823	GN 22-120-M20-100-D0-TK	120	M 20	12	32	100	15	28	1145
GN.80825	GN 22-120-M20-125-D0-TK	120	M 20	12	32	125	15	28	1205
GN.80827	GN 22-120-M20-150-D0-TK	120	M 20	12	32	150	15	28	1265
GN.80829	GN 22-120-M20-200-D0-TK	120	M 20	12	32	200	15	28	1390
GN.80831	GN 22-120-M20-250-D0-TK	120	M 20	12	32	250	15	28	1510
GN.80841	GN 22-120-M24-100-D0-TK	120	M 24	12	35.5	100	19	46	1320
GN.80843	GN 22-120-M24-125-D0-TK	120	M 24	12	35.5	125	19	46	1410
GN.80845	GN 22-120-M24-150-D0-TK	120	M 24	12	35.5	150	19	46	1495
GN.80847	GN 22-120-M24-200-D0-TK	120	M 24	12	35.5	200	19	46	1675
GN.80849	GN 22-120-M24-300-D0-TK	120	M 24	12	35.5	300	19	46	2025

GN 22-D1-TK



GN 22-D1-TK

Code	Description	d1	d2	h1	h2	h4	l1	sw2	Static load [KN]	⚖️
GN.80682	GN 22-80-M16-75-D1-TK	80	M 16	8.5	2	25.5	75	12	17	436
GN.80684	GN 22-80-M16-100-D1-TK	80	M 16	8.5	2	25.5	100	12	17	476
GN.80686	GN 22-80-M16-125-D1-TK	80	M 16	8.5	2	25.5	125	12	17	515
GN.80688	GN 22-80-M16-150-D1-TK	80	M 16	8.5	2	25.5	150	12	17	554
GN.80690	GN 22-80-M16-200-D1-TK	80	M 16	8.5	2	25.5	200	12	17	633
GN.80692	GN 22-80-M16-250-D1-TK	80	M 16	8.5	2	25.5	250	12	17	711
GN.80702	GN 22-80-M20-75-D1-TK	80	M 20	8.5	2	27	75	15	28	549
GN.80704	GN 22-80-M20-100-D1-TK	80	M 20	8.5	2	27	100	15	28	611
GN.80706	GN 22-80-M20-125-D1-TK	80	M 20	8.5	2	27	125	15	28	672
GN.80708	GN 22-80-M20-150-D1-TK	80	M 20	8.5	2	27	150	15	28	733
GN.80710	GN 22-80-M20-200-D1-TK	80	M 20	8.5	2	27	200	15	28	856
GN.80712	GN 22-80-M20-250-D1-TK	80	M 20	8.5	2	27	250	15	28	978
GN.80722	GN 22-80-M24-100-D1-TK	80	M 24	8.5	2	30.5	100	19	46	795
GN.80724	GN 22-80-M24-125-D1-TK	80	M 24	8.5	2	30.5	125	19	46	884
GN.80726	GN 22-80-M24-150-D1-TK	80	M 24	8.5	2	30.5	150	19	46	972
GN.80728	GN 22-80-M24-200-D1-TK	80	M 24	8.5	2	30.5	200	19	46	1150
GN.80730	GN 22-80-M24-300-D1-TK	80	M 24	8.5	2	30.5	300	19	46	1500
GN.80762	GN 22-100-M16-75-D1-TK	100	M 16	9	3	26.5	75	12	17	637
GN.80764	GN 22-100-M16-100-D1-TK	100	M 16	9	3	26.5	100	12	17	676
GN.80766	GN 22-100-M16-125-D1-TK	100	M 16	9	3	26.5	125	12	17	715
GN.80768	GN 22-100-M16-150-D1-TK	100	M 16	9	3	26.5	150	12	17	754
GN.80770	GN 22-100-M16-200-D1-TK	100	M 16	9	3	26.5	200	12	17	833
GN.80772	GN 22-100-M16-250-D1-TK	100	M 16	9	3	26.5	250	12	17	911
GN.80782	GN 22-100-M20-75-D1-TK	100	M 20	9	3	28	75	15	28	748
GN.80784	GN 22-100-M20-100-D1-TK	100	M 20	9	3	28	100	15	28	809
GN.80786	GN 22-100-M20-125-D1-TK	100	M 20	9	3	28	125	15	28	870
GN.80788	GN 22-100-M20-150-D1-TK	100	M 20	9	3	28	150	15	28	932
GN.80790	GN 22-100-M20-200-D1-TK	100	M 20	9	3	28	200	15	28	1055
GN.80792	GN 22-100-M20-250-D1-TK	100	M 20	9	3	28	250	15	28	1175
GN.80808	GN 22-100-M24-100-D1-TK	100	M 24	9	3	31.5	100	19	46	995
GN.80810	GN 22-100-M24-125-D1-TK	100	M 24	9	3	31.5	125	19	46	1085
GN.80812	GN 22-100-M24-150-D1-TK	100	M 24	9	3	31.5	150	19	46	1170
GN.80814	GN 22-100-M24-200-D1-TK	100	M 24	9	3	31.5	200	19	46	1350
GN.80816	GN 22-100-M24-300-D1-TK	100	M 24	9	3	31.5	300	19	46	1700
GN.80822	GN 22-120-M20-75-D1-TK	120	M 20	12	3.5	32	75	15	28	1160
GN.80824	GN 22-120-M20-100-D1-TK	120	M 20	12	3.5	32	100	15	28	1225
GN.80826	GN 22-120-M20-125-D1-TK	120	M 20	12	3.5	32	125	15	28	1285
GN.80828	GN 22-120-M20-150-D1-TK	120	M 20	12	3.5	32	150	15	28	1345
GN.80830	GN 22-120-M20-200-D1-TK	120	M 20	12	3.5	32	200	15	28	1470
GN.80832	GN 22-120-M20-250-D1-TK	120	M 20	12	3.5	32	250	15	28	1590
GN.80842	GN 22-120-M24-100-D1-TK	120	M 24	12	3.5	35.5	100	19	46	1400
GN.80844	GN 22-120-M24-125-D1-TK	120	M 24	12	3.5	35.5	125	19	46	1490
GN.80846	GN 22-120-M24-150-D1-TK	120	M 24	12	3.5	35.5	150	19	46	1575
GN.80848	GN 22-120-M24-200-D1-TK	120	M 24	12	3.5	35.5	200	19	46	1755
GN.80850	GN 22-120-M24-300-D1-TK	120	M 24	12	3.5	35.5	300	19	46	2105

INOX STAINLESS STEEL

