

LEVER BODY

Die-cast zinc alloy with epoxy resin coating, sand-blasted matte finish.

STANDARD EXECUTIONS

Retaining screw with six-lobed socket to fit TORX®\* (see communication attached).

Steel return spring. Black-oxide steel clamping element and retaining screw.

- GN 300 (d1): threaded hole.
- GN 300 (d1 - I2): threaded screw.

FEATURES AND APPLICATIONS

Particularly suitable when the lever turning angle is limited owing to lack of space.


INSTRUCTIONS OF USE

For clamping, lift the lever to disengage the clamping device teeth and bring it back to start position. By releasing the lever, the return spring automatically engages the teeth.

If the lever cannot make a 360° rotation, the clamping element can be easily screwed by means of the six-lobed socket front head screw (after having disengaged the lever).

SPECIAL EXECUTIONS ON REQUEST

- Lever body in different colours.
- Chrome-plated lever.
- Clamping element with different threadings and lengths.




\* Complete with colour index of the lever body (SW, OS, GR)

|         |         |         |
|---------|---------|---------|
| SW      | OS      | GR      |
| RAL9005 | RAL2004 | RAL7031 |

GN 300 (d1)

| Code SW  | Code OS  | Code GR  | Description     | l1  | d1  | d3   | d4   | h1   | h2  | h3 | h4  | tmin | ⚖   |
|----------|----------|----------|-----------------|-----|-----|------|------|------|-----|----|-----|------|-----|
| GN.15801 | GN.15802 | -        | GN 300-30-M3*   | 30  | M3  | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 7    | 15  |
| GN.15806 | GN.15807 | -        | GN 300-30-M4*   | 30  | M4  | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 7    | 15  |
| GN.15811 | GN.15812 | -        | GN 300-30-M5*   | 30  | M5  | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 7    | 15  |
| GN.15816 | GN.15817 | -        | GN 300-30-M6*   | 30  | M6  | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 7    | 15  |
| GN.16101 | GN.16102 | GN.16104 | GN 300-45-M5*   | 45  | M5  | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 9    | 34  |
| GN.16111 | GN.16112 | GN.16114 | GN 300-45-M6*   | 45  | M6  | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 9    | 33  |
| GN.16121 | GN.16122 | GN.16124 | GN 300-63-M6*   | 63  | M6  | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 11   | 76  |
| GN.16131 | GN.16132 | GN.16134 | GN 300-63-M8*   | 63  | M8  | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 11   | 74  |
| GN.16141 | GN.16142 | GN.16144 | GN 300-78-M8*   | 78  | M8  | 16   | 21   | 36   | 8   | 55 | 4   | 14   | 123 |
| GN.16151 | GN.16152 | GN.16154 | GN 300-78-M10*  | 78  | M10 | 16   | 21   | 36   | 8   | 55 | 4   | 17   | 194 |
| GN.16161 | GN.16162 | GN.16164 | GN 300-92-M10*  | 92  | M10 | 19   | 24   | 43   | 11  | 65 | 4   | 17   | 194 |
| GN.16171 | GN.16172 | GN.16174 | GN 300-92-M12*  | 92  | M12 | 19   | 24   | 43   | 11  | 65 | 4   | 17   | 171 |
| GN.16181 | GN.16182 | GN.16184 | GN 300-108-M12* | 108 | M12 | 23   | 30   | 50.5 | 12  | 76 | 5   | 22   | 306 |
| GN.16185 | GN.16186 | GN.16188 | GN 300-108-M14* | 108 | M14 | 23   | 30   | 50.5 | 12  | 76 | 5   | 22   | 298 |
| GN.16191 | GN.16192 | GN.16194 | GN 300-108-M16* | 108 | M16 | 23   | 30   | 50.5 | 12  | 76 | 5   | 22   | 306 |




\* Complete with colour index of the lever body (SW, OS, GR)

SW RAL9005 OS RAL2004 GR RAL7031

GN 300 (d1 - l2)

| Code SW  | Code OS  | Code GR  | Description       | l1 | d1 | d3   | d4   | h1   | h2  | h3 | h4  | l2 | △  |
|----------|----------|----------|-------------------|----|----|------|------|------|-----|----|-----|----|----|
| GN.15831 | GN.15832 | -        | GN 300-30-M3-6-*  | 30 | M3 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 6  | 26 |
| GN.15836 | GN.15837 | -        | GN 300-30-M3-8-*  | 30 | M3 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 8  | 26 |
| GN.15841 | GN.15842 | -        | GN 300-30-M3-10-* | 30 | M3 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 10 | 26 |
| GN.15846 | GN.15847 | -        | GN 300-30-M3-12-* | 30 | M3 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 12 | 26 |
| GN.15851 | GN.15852 | -        | GN 300-30-M3-16-* | 30 | M3 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 16 | 26 |
| GN.15861 | GN.15862 | -        | GN 300-30-M4-12-* | 30 | M4 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 12 | 27 |
| GN.15866 | GN.15867 | -        | GN 300-30-M4-16-* | 30 | M4 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 16 | 27 |
| GN.15871 | GN.15872 | -        | GN 300-30-M4-20-* | 30 | M4 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 20 | 27 |
| GN.15876 | GN.15877 | -        | GN 300-30-M4-25-* | 30 | M4 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 25 | 28 |
| GN.15881 | GN.15882 | -        | GN 300-30-M4-32-* | 30 | M4 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 32 | 28 |
| GN.15901 | GN.15902 | -        | GN 300-30-M5-12-* | 30 | M5 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 12 | 28 |
| GN.15906 | GN.15907 | -        | GN 300-30-M5-16-* | 30 | M5 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 16 | 28 |
| GN.15911 | GN.15912 | -        | GN 300-30-M5-20-* | 30 | M5 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 20 | 29 |
| GN.15916 | GN.15917 | -        | GN 300-30-M5-25-* | 30 | M5 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 25 | 29 |
| GN.15921 | GN.15922 | -        | GN 300-30-M5-32-* | 30 | M5 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 32 | 30 |
| GN.15926 | GN.15927 | -        | GN 300-30-M5-40-* | 30 | M5 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 40 | 31 |
| GN.15931 | GN.15932 | -        | GN 300-30-M5-50-* | 30 | M5 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 50 | 32 |
| GN.15951 | GN.15952 | -        | GN 300-30-M6-12-* | 30 | M6 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 12 | 29 |
| GN.15956 | GN.15957 | -        | GN 300-30-M6-16-* | 30 | M6 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 16 | 29 |
| GN.15961 | GN.15962 | -        | GN 300-30-M6-20-* | 30 | M6 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 20 | 30 |
| GN.15966 | GN.15967 | -        | GN 300-30-M6-25-* | 30 | M6 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 25 | 31 |
| GN.15971 | GN.15972 | -        | GN 300-30-M6-32-* | 30 | M6 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 32 | 32 |
| GN.15976 | GN.15977 | -        | GN 300-30-M6-40-* | 30 | M6 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 40 | 33 |
| GN.15981 | GN.15982 | -        | GN 300-30-M6-50-* | 30 | M6 | 10   | 13   | 24.5 | 4   | 31 | 3.5 | 50 | 34 |
| GN.16201 | GN.16202 | GN.16204 | GN 300-45-M6-12-* | 45 | M6 | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 12 | 36 |
| GN.16211 | GN.16212 | GN.16214 | GN 300-45-M6-16-* | 45 | M6 | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 16 | 37 |
| GN.16221 | GN.16222 | GN.16224 | GN 300-45-M6-20-* | 45 | M6 | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 20 | 37 |
| GN.16231 | GN.16232 | GN.16234 | GN 300-45-M6-25-* | 45 | M6 | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 25 | 38 |
| GN.16241 | GN.16242 | GN.16244 | GN 300-45-M6-32-* | 45 | M6 | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 32 | 40 |
| GN.16251 | GN.16252 | GN.16254 | GN 300-45-M6-40-* | 45 | M6 | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 40 | 41 |
| GN.16261 | GN.16262 | GN.16264 | GN 300-45-M6-50-* | 45 | M6 | 10   | 13   | 24.5 | 4   | 35 | 3.5 | 50 | 43 |
| GN.16271 | GN.16272 | GN.16274 | GN 300-63-M8-16-* | 63 | M8 | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 16 | 83 |
| GN.16281 | GN.16282 | GN.16284 | GN 300-63-M8-20-* | 63 | M8 | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 20 | 84 |
| GN.16291 | GN.16292 | GN.16294 | GN 300-63-M8-25-* | 63 | M8 | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 25 | 86 |
| GN.16301 | GN.16302 | GN.16304 | GN 300-63-M8-32-* | 63 | M8 | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 32 | 88 |
| GN.16311 | GN.16312 | GN.16314 | GN 300-63-M8-40-* | 63 | M8 | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 40 | 91 |
| GN.16321 | GN.16322 | GN.16324 | GN 300-63-M8-50-* | 63 | M8 | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 50 | 93 |
| GN.16331 | GN.16332 | GN.16334 | GN 300-63-M8-63-* | 63 | M8 | 13.5 | 17.5 | 31   | 6.5 | 45 | 4   | 63 | 98 |



\* Complete with colour index of the lever body (SW, OS, GR)



GN 300 (d1 - l2)

| Code SW  | Code OS  | Code GR  | Description         | l1  | d1  | d3 | d4 | h1   | h2 | h3 | h4 | l2 |     |
|----------|----------|----------|---------------------|-----|-----|----|----|------|----|----|----|----|-----|
| GN.16341 | GN.16342 | GN.16344 | GN 300-78-M10-20-*  | 78  | M10 | 16 | 21 | 36   | 8  | 55 | 4  | 20 | 139 |
| GN.16351 | GN.16352 | GN.16354 | GN 300-78-M10-25-*  | 78  | M10 | 16 | 21 | 36   | 8  | 55 | 4  | 25 | 141 |
| GN.16361 | GN.16362 | GN.16364 | GN 300-78-M10-32-*  | 78  | M10 | 16 | 21 | 36   | 8  | 55 | 4  | 32 | 142 |
| GN.16371 | GN.16372 | GN.16374 | GN 300-78-M10-40-*  | 78  | M10 | 16 | 21 | 36   | 8  | 55 | 4  | 40 | 146 |
| GN.16381 | GN.16382 | GN.16384 | GN 300-78-M10-50-*  | 78  | M10 | 16 | 21 | 36   | 8  | 55 | 4  | 50 | 152 |
| GN.16391 | GN.16392 | GN.16394 | GN 300-78-M10-63-*  | 78  | M10 | 16 | 21 | 36   | 8  | 55 | 4  | 63 | 159 |
| GN.16401 | GN.16402 | GN.16404 | GN 300-78-M10-80-*  | 78  | M10 | 16 | 21 | 36   | 8  | 55 | 4  | 80 | 166 |
| GN.16601 | GN.16602 | GN.16604 | GN 300-78-M12-25-*  | 78  | M12 | 16 | 21 | 36   | 8  | 55 | 4  | 25 | 145 |
| GN.16611 | GN.16612 | GN.16614 | GN 300-78-M12-32-*  | 78  | M12 | 16 | 21 | 36   | 8  | 55 | 4  | 32 | 150 |
| GN.16621 | GN.16622 | GN.16624 | GN 300-78-M12-40-*  | 78  | M12 | 16 | 21 | 36   | 8  | 55 | 4  | 40 | 156 |
| GN.16631 | GN.16632 | GN.16634 | GN 300-78-M12-50-*  | 78  | M12 | 16 | 21 | 36   | 8  | 55 | 4  | 50 | 163 |
| GN.16641 | GN.16642 | GN.16644 | GN 300-78-M12-63-*  | 78  | M12 | 16 | 21 | 36   | 8  | 55 | 4  | 63 | 171 |
| GN.16651 | GN.16652 | GN.16654 | GN 300-78-M12-80-*  | 78  | M12 | 16 | 21 | 36   | 8  | 55 | 4  | 80 | 183 |
| GN.16411 | GN.16412 | GN.16414 | GN 300-92-M12-25-*  | 92  | M12 | 19 | 24 | 43   | 11 | 65 | 4  | 25 | 212 |
| GN.16421 | GN.16422 | GN.16424 | GN 300-92-M12-32-*  | 92  | M12 | 19 | 24 | 43   | 11 | 65 | 4  | 32 | 217 |
| GN.16431 | GN.16432 | GN.16434 | GN 300-92-M12-40-*  | 92  | M12 | 19 | 24 | 43   | 11 | 65 | 4  | 40 | 222 |
| GN.16441 | GN.16442 | GN.16444 | GN 300-92-M12-50-*  | 92  | M12 | 19 | 24 | 43   | 11 | 65 | 4  | 50 | 229 |
| GN.16451 | GN.16452 | GN.16454 | GN 300-92-M12-63-*  | 92  | M12 | 19 | 24 | 43   | 11 | 65 | 4  | 63 | 239 |
| GN.16461 | GN.16462 | GN.16464 | GN 300-92-M12-80-*  | 92  | M12 | 19 | 24 | 43   | 11 | 65 | 4  | 80 | 250 |
| GN.16471 | GN.16472 | GN.16474 | GN 300-108-M16-32-* | 108 | M16 | 23 | 30 | 50.5 | 12 | 76 | 5  | 32 | 365 |
| GN.16481 | GN.16482 | GN.16484 | GN 300-108-M16-40-* | 108 | M16 | 23 | 30 | 50.5 | 12 | 76 | 5  | 40 | 376 |
| GN.16491 | GN.16492 | GN.16494 | GN 300-108-M16-50-* | 108 | M16 | 23 | 30 | 50.5 | 12 | 76 | 5  | 50 | 388 |
| GN.16501 | GN.16502 | GN.16504 | GN 300-108-M16-63-* | 108 | M16 | 23 | 30 | 50.5 | 12 | 76 | 5  | 63 | 407 |
| GN.16511 | GN.16512 | GN.16514 | GN 300-108-M16-80-* | 108 | M16 | 23 | 30 | 50.5 | 12 | 76 | 5  | 80 | 429 |