

GUIDE TUBE

Chrome-plated steel.

SHAFT

Natural steel.

END CAPS


Polyamide based (PA) technopolymer.

FEATURES AND APPLICATIONS


GN 391 connecting units are used with linear actuators GN 291 (see page 1374) and GN 292 (see page 1373).

They are used to transfer the linear actuator rotating movement to a different position.



By using GN 297 (see page) angular gear it is possible to rotate the linear actuator operating axis by 90°.



Guide elements



Transfer units



Code	Description	d1	d2	l1	l1*	l2	△
GN.67956	GN 391-18-47-SCR	18	6	47	42 ... 500	16	63
GN.67966	GN 391-30-60-SCR	30	8	60	55 ... 2000	16	180
GN.67976	GN 391-40-93-SCR	40	12	93	88 ... 2500	17	506
GN.67986	GN 391-50-93-SCR	50	12	93	88 ... 2500	18	781
GN.67996	GN 391-60-95-SCR	60	14	95	90 ... 2800	19	1165

* (available upon request)