Ball transfer units

With mounting flange, steel sheet

RoHS


HOUSING
Steel sheet **S**
Zinc-plated, blue passivated

BALL
- Steel, smooth finish **BL**
- INOX AISI 420C stainless steel **NI**
- Technopolymer, polyacetal (POM) **KU**

BEARING BALLS
- Steel, smooth finish for load ball BL/KU
- AISI 420C stainless steel for load ball NI

INFORMATION
GN 509.8 ball transfer units are used, for example, in conveyors or on packaging tables to move heavy loads in any direction with minimal effort. The ball roller bearing ensures reliable operation and long life. The ball transfer units are fastened using the mounting flange.





GN 509.8

Code	Description	Size	d_1	d_2	d_3 ±0.4	d_4	d_5	h_1 ±0.4	h_2 ±0.4	h_3	Load C in N Static	⚖
GN.45691	GN 509.8-15-SBL	15	15.8	24	41	30	3.5	19.6	10.8	3.4	150	45
GN.45692	GN 509.8-15-SKU	15	15.8	24	41	30	3.5	19.6	10.8	3.4	100	34
GN.45693	GN 509.8-15-SNI	15	15.8	24	41	30	3.5	19.6	10.8	3.4	150	45
GN.45694	GN 509.8-25-SBL	25	25.4	38	56	45	4	30	14.6	3.4	600	130
GN.45695	GN 509.8-25-SKU	25	25.4	38	56	45	4	30	14.6	3.4	200	75
GN.45696	GN 509.8-25-SNI	25	25.4	38	56	45	4	30	14.6	3.4	600	130

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.
Ganter Norm