



MATERIAL

Black-oxide steel, class 5.8 (tensile strength 500 N/mm²).

FEATURES AND APPLICATIONS

GN 551.1 threaded studs can be coupled to clamping knobs with tapped bosses, when a clamping nut has to be changed to a clamping thread screw.

Application examples



Code	Description	d	l	⚖
GN.13102	GN 551.1-M6-20	M6	20	4
GN.13103	GN 551.1-M6-25	M6	25	4
GN.13104	GN 551.1-M6-30	M6	30	5
GN.13105	GN 551.1-M6-35	M6	35	6
GN.13106	GN 551.1-M6-40	M6	40	7
GN.13107	GN 551.1-M6-45	M6	45	8
GN.13108	GN 551.1-M6-50	M6	50	9
GN.13109	GN 551.1-M6-60	M6	60	11
GN.13111	GN 551.1-M8-25	M8	25	7
GN.13112	GN 551.1-M8-30	M8	30	9
GN.13113	GN 551.1-M8-35	M8	35	11
GN.13114	GN 551.1-M8-40	M8	40	12
GN.13115	GN 551.1-M8-45	M8	45	14
GN.13116	GN 551.1-M8-50	M8	50	15
GN.13117	GN 551.1-M8-60	M8	60	19
GN.13118	GN 551.1-M8-70	M8	70	21
GN.13119	GN 551.1-M8-80	M8	80	24
GN.13121	GN 551.1-M10-25	M10	25	12
GN.13122	GN 551.1-M10-30	M10	30	14
GN.13123	GN 551.1-M10-35	M10	35	16
GN.13124	GN 551.1-M10-40	M10	40	19
GN.13125	GN 551.1-M10-45	M10	45	21
GN.13126	GN 551.1-M10-50	M10	50	24
GN.13127	GN 551.1-M10-60	M10	60	29
GN.13128	GN 551.1-M10-70	M10	70	34
GN.13129	GN 551.1-M10-80	M10	80	38

Code	Description	d	l	⚖
GN.13131	GN 551.1-M12-30	M12	30	21
GN.13132	GN 551.1-M12-35	M12	35	24
GN.13133	GN 551.1-M12-40	M12	40	27
GN.13134	GN 551.1-M12-45	M12	45	31
GN.13135	GN 551.1-M12-50	M12	50	34
GN.13136	GN 551.1-M12-60	M12	60	41
GN.13137	GN 551.1-M12-70	M12	70	48
GN.13138	GN 551.1-M12-80	M12	80	55
GN.13139	GN 551.1-M12-100	M12	100	69
GN.13141	GN 551.1-M16-30	M16	30	38
GN.13142	GN 551.1-M16-35	M16	35	43
GN.13143	GN 551.1-M16-40	M16	40	48
GN.13144	GN 551.1-M16-45	M16	45	56
GN.13145	GN 551.1-M16-50	M16	50	63
GN.13146	GN 551.1-M16-60	M16	60	76
GN.13147	GN 551.1-M16-70	M16	70	84
GN.13148	GN 551.1-M16-80	M16	80	102
GN.13149	GN 551.1-M16-100	M16	100	128
GN.13152	GN 551.1-M20-40	M20	40	79
GN.13154	GN 551.1-M20-50	M20	50	98
GN.13155	GN 551.1-M20-60	M20	60	118
GN.13156	GN 551.1-M20-70	M20	70	139
GN.13157	GN 551.1-M20-80	M20	80	159
GN.13158	GN 551.1-M20-100	M20	100	199