


SPECIFICATION


- AISI 316
- Sand-blasted matte finish. **MT**
- Polished finish **PL**

FEATURES AND APPLICATIONS


Stainless steel T-handles GN 5063 are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces. The T-handles can also be used in particularly aggressive environments thanks to the materials used



GN 5063 (d2)



GN 5063 (d3)



GN 5063-MT (d2)



Code	Description	d1	d2	d4	b	h1	h2	tmin	△
GN.21855	GN 5063-63-M6-MT	63	M6	16	7	41	12	12	111
GN.21857	GN 5063-63-M8-MT	63	M8	16	7	41	12	16	108
GN.21873	GN 5063-80-M8-MT	80	M8	21	9	52	15	16	225
GN.21877	GN 5063-80-M10-MT	80	M10	21	9	52	15	20	220
GN.21895	GN 5063-100-M10-MT	100	M10	25	11	65	19	20	432
GN.21897	GN 5063-100-M12-MT	100	M12	25	11	65	19	24	425

GN 5063-MT (d3)

Code	Description	d1	d3 H9	d4	b	h1	h2	tmin	△
GN.21851	GN 5063-63-B6-MT	63	6	16	7	41	12	12	110
GN.21853	GN 5063-63-B8-MT	63	8	16	7	41	12	16	106
GN.21871	GN 5063-80-B8-MT	80	8	21	9	52	15	16	223
GN.21875	GN 5063-80-B10-MT	80	10	21	9	52	15	20	216
GN.21891	GN 5063-100-B10-MT	100	10	25	11	65	19	20	429
GN.21893	GN 5063-100-B12-MT	100	12	25	11	65	19	24	419

GN 5063-PL (d2)



Code	Description	d1	d2	d4	b	h1	h2	tmin	△
GN.21856	GN 5063-63-M6-PL	63	M6	16	7	41	12	12	111
GN.21858	GN 5063-63-M8-PL	63	M8	16	7	41	12	16	108
GN.21874	GN 5063-80-M8-PL	80	M8	21	9	52	15	16	225
GN.21878	GN 5063-80-M10-PL	80	M10	21	9	52	15	20	220
GN.21896	GN 5063-100-M10-PL	100	M10	25	11	65	19	20	432
GN.21898	GN 5063-100-M12-PL	100	M12	25	11	65	19	24	425

GN 5063-PL (d3)

Code	Description	d1	d3 H9	d4	b	h1	h2	tmin	△
GN.21851	GN 5063-63-B6-MT	63	6	16	7	41	12	12	110
GN.21853	GN 5063-63-B8-MT	63	8	16	7	41	12	16	106
GN.21871	GN 5063-80-B8-MT	80	8	21	9	52	15	16	223
GN.21875	GN 5063-80-B10-MT	80	10	21	9	52	15	20	216
GN.21891	GN 5063-100-B10-MT	100	10	25	11	65	19	20	429
GN.21893	GN 5063-100-B12-MT	100	12	25	11	65	19	24	419